

USB-C USB-A Dock - Hybrid Universal USB 3.0 Docking Station for USB-C or USB-A Laptop - Dual Monitor 4K 60Hz HDMI/DisplayPort - 6x USB-A, GbE - USB 3.1/3.2 Gen 1 - Windows/Mac

**Product ID:** DK30A2DHU



Transition from the legacy USB-A (USB 3.1/3.0) to newer USB-C laptops with this universal laptop docking station for USB-C and USB-A laptops. The USB 3.1 Gen 1 (5 Gbps) Type-C dock features dual HDMI and/or DisplayPort monitors, six USB Type-A downstream peripheral ports, and headset audio.

This is a dual 4K60Hz video docking station with support for both Ultra HD DisplayPort and/or HDMI monitors that lets you configure your video connections to best suit your needs.

Dual 4K DisplayPort Up to 4096 x 2160p @ 60Hz

Dual 4K HDMI Up to 4096 x 2160p @ 60Hz

Single 4K DisplayPort + Single 4K HDMI Up to 4096 x 2160p @ 60Hz

Single 5K DisplayPort\* Up to 5120 2880

\*Requires monitor support for 5K using two DP ports

This docking station is fully certified to meet top industry standards for DisplayLink (video connections) certification to guarantee the highest quality, performance, and compatibility.

For fast setup right out of the box, the two included host cables (USB-C and USB-A) connect to any laptop. The included dock stand lets you position the dock vertically to save space or lay flat on the desk.

Connect your devices with six downstream USB Type-A (USB 3.0 5 Gbps) ports, two positioned on the front, and four on the back. The dock provides a GbE port and a 3.5 mm 4-position headset audio jack.

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the market that works with a wide range of IT connectivity accessories. The software suite includes:

Advanced Windows Layout Utility: To setup and save custom windows layouts.

Mac Address Pass-Through Utility: To improve network security.

USB Event Monitoring Utility: To track and log connected USB devices

Wi-Fi Auto Switch Utility: Enabling users to quickly access faster network speeds via wired LAN.

For more information and to download the StarTech.com Connectivity Tools application, please visit:  
[www.StarTech.com/Connectivity-Tools](http://www.StarTech.com/Connectivity-Tools)

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

DK30A2DHU is backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

### Features

- **LATEST MODEL:** This USB-C USB-A dock offers the same functionality as DK30A2DH, with added flexibility of horizontal or vertical orientation using the included stand to save space at your workstation
- **HYBRID DOCK:** Universal USB 3.0 docking station works w/ USB-C & USB-A laptops/computers and features a 6-Port USB Type-A hub, Gigabit Ethernet & headset audio jack; NOTE: This dock does not provide USB-C Power Delivery to charge your laptop
- **FLEXIBLE DUAL MONITOR VIDEO:** This 4K 60Hz USB-C or USB-A docking station can connect up to 2 monitors: Dual DisplayPort or Dual HDMI or DP + HDMI displays; supports dual extended displays on MacBooks with both the Intel processor or Apple M1/M2 chip
- **6 DOWNSTREAM USB-A PORTS:** Hybrid USB C dock has a 6-port USB 3.1/3.2 Gen 1 (5Gbps) hub w/ extra USB-A ports to support devices such as keyboard, mouse, flash drive, external hard drive & printer

- **COMPATIBILITY:** USB-C port replicator is DisplayLink Certified for max. performance & compatible w/ Dell, HP, Lenovo & MacBook PCs; Windows, ChromeOS and macOS platforms, where mixed laptop Brands used; Includes USB-C and USB-A host cables
- **CONNECTIVITY TOOLS:** Provided with this device, the application improves performance and security, featuring MAC Address Changer, USB Event Monitoring, Windows Layout & Wi-Fi Auto Switch utilities

---

## Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	No
Displays Supported	2
Ports	8
Audio	Yes
Interface	USB 3.2 Gen 1
Bus Type	USB-C
USB Pass-Through	Yes
Chipset ID	DisplayLink - DL-6950 VIA/VLI - VL813 Realtek - RTS5411T

---

## Performance

Maximum Digital Resolutions	4K 60Hz
General Specifications	Wake-on-LAN (WoL): Yes
MTBF	26 280 hrs

---

## Connector(s)

Connector Type(s)	6 - USB 3.2 Type-A (9 pin, Gen 1, 5Gbps) 1 - RJ-45 2 - HDMI 2 - DisplayPort
-------------------	--

	1 - 3.5 mm Audio
Host Connectors	1 - USB 3.2 USB Type-B (9 pin, Gen 1, 5 Gbps)

---

#### Software

OS Compatibility	Windows XP (32-bit), Vista, 7, 8, 8.1, 10, 11, macOS 10.6 - 10.12, 10.14 - 10.15, 11.0, 12.0, 13.0, 14.0, Chrome OS v55+
------------------	--

---

#### Special Notes / Requirements

Note	DisplayLink docking stations and video adapters support more than one external display on Apple's M1-based Mac. Requires driver installation. Please contact StarTech.com support for a recommendation based on your specific setup.
------	--

---

#### Power

Power Source	AC Adapter Included
Input Voltage	110V-240V AC
Input Current	1.0A
Output Voltage	20V DC
Output Current	2A
Plug Type	N
Power Consumption (In Watts)	40W

---

#### Environmental

Operating Temperature	0 to 50C
Storage Temperature	-20 to 70C
Humidity	0% to 95% (non-condensing) at 25C

---

#### Physical Characteristics

Color	Black & Gray
Material	Aluminum and Plastic
Cable Length	3.3 ft [1 m]
Product Length	2.9 in [7.3 cm]
Product Width	5.3 in [13.5 cm]

Product Height	7.4 in [18.7 cm]
Weight of Product	12.0 oz [340.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.3 in [21.2 cm]
Package Width	4.5 in [11.4 cm]
Package Height	5.7 in [14.4 cm]
Shipping (Package) Weight	1.7 lb [0.8 kg]

---

**What's in the Box**

Included in Package	1 - Docking Station
	1 - USB-C to USB-B Cable
	1 - USB-A to USB-B Cable
	1 - Universal Power Adapter (NA/JP, ANZ)
	1 - Dock Stand
	1 - Quick-Start Guide

---

***\*Product appearance and specifications are subject to change without notice.***