

USB-C Dock - Single Monitor 4K 30Hz HDMI Laptop Docking Station with 85W Power Delivery, 4pt USB 3.0 Hub, Gb Ethernet, Audio - Compact USB 3.1 Gen 1 Type-C Dock - Mac & PC

Product ID: DK30CHDPD



This USB-C dock gives you all the connections you need to turn your USB-C enabled laptop or tablet into a fully capable workstation, with support for a single external 4K HDMI monitor or ultrawide monitor. With USB Power Delivery 2.0 (85W), you can power and charge your laptop as you work, eliminating the need to use a separate power adapter with your laptop. It's the perfect companion for your MacBook Pro or other Thunderbolt 3 equipped laptop or tablet.

The USB-C dock helps you maximize your workspace, ideal for smaller or shared work areas using one monitor. The dock expands the display capabilities of your laptop, connecting to an HDMI display with support for resolutions including: 4096x2160 @ 30Hz, 3840 x 2160 @ 30Hz, 2560x1600 @60 Hz, 1920 x 1200 @ 60Hz.

Create an immersive experience by connecting the USB-C dock to an ultrawide or ultrawide curved monitor with 21:9 aspect ratio (3440 x 1440p @ 60 Hz), to emulate a multi-display set-up and gain exceptional picture quality.

The dock provides four USB 3.0 (Type-A) ports to connect peripherals such as your mouse or keyboard. It also includes a USB 3.0 fast-charge and sync port, a Gigabit Ethernet port (with PXE Boot support) and a combined 3.5 mm audio and microphone port.

Compatible with Mac and Windows, this universal dock works with USB-C and Thunderbolt 3 enabled laptops.

The DK30CHDPD is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- A cost-effective docking station solution for business and office environments, where most employees use only a single external monitor

- Effective in small workspaces or cubicle environments with limited space for multiple displays
- Ideal for temporary or shared workspaces (hoteling) where only one external monitor is required
- Connect to an ultrawide or ultrawide curved monitor to emulate a multi-display experience view and gain exceptional picture quality

Features

- **COMPACT FULL FEATURE DOCK:** This USB-C dock features single 4K 30Hz HDMI video, 85W PD, 4x USB-A 3.0 (5Gbps) ports (1 fast charge), Gigabit Ethernet, a headset/audio port & 1m/3.3 ft USB-C cable
- **WIDE DEVICE COMPATIBILITY:** USB C dock supports USB-C/Thunderbolt 3 (TB3) laptops like HP, Dell, Lenovo, Surface Laptop 3 & Pro 7, Chromebook, MacBook Pro, MacBook Air, iPad Pro, Samsung, Google Pixel
- **85W POWER DELIVERY:** The USB 3.1 Gen 1 Type-C docking station will quickly charge workstation laptops like Lenovo ThinkPad P Series, HP Z Books & MacBook Pro 15/16, where more power is required
- **COMPACT SIZE:** Designed for small workspaces or work from home, this USB-C laptop port replicator is ideal for single monitor or ultra-wide monitor workstation setups
- **WIDE OPERATING SYSTEM COMPATIBILITY:** Automatic driver installation; universal USB-C dock is compatible with major OS platforms like Windows, MacOS, Chrome OS, iPadOS, and Android phones

Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	Yes
Displays Supported	1
Interface	USB 3.0
Bus Type	USB-C
Industry Standards	USB Power Delivery Specification Rev. 2.0 USB Battery Charging Specification Rev. 1.2 DisplayPort 1.2 IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0 and 1.1
Chipset ID	Parade - PS176 Realtek - RTL8153

Realtek - RTS5411

C-Media - CM6533

Performance

Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
Maximum Digital Resolutions	HDMI - 4096x2160 @ 30Hz, 3840 x 2160 @ 30Hz, 2560x1600 @60 Hz, 1920 x 1200 @ 60Hz UltraWide - 3440 x 1440p @ 60 Hz
Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
PXE	Yes
Full Duplex Support	Yes

Connector(s)

Connector Type(s)	HDMI (19 pin) USB Type-C (24 pin) USB 3.0 (5Gbps) USB 3.0 A (Fast-Charge, 9 pin) USB Type-A (9 pin) USB 3.0 (5 Gbps) RJ-45 3.5 mm Mini-Jack (4 Position)
-------------------	---

Software

OS Compatibility	Windows 7, 8, 8.1, 10 macOS 10.11 to 10.15, 11.0
------------------	---

Special Notes / Requirements

System and Cable Requirements	USB-C enabled computer with an available USB Type-C port
-------------------------------	--



Note

Not all USB-C ports support the full functionality of the USB Type-C standard. Ensure that your host USB-C port supports USB Power Delivery 2.0 and DP alt mode.

Supports 4K resolution. A 4K-capable HDMI display is required to achieve 4Kx2K resolution.

USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps

Power

Power Source	AC Adapter Included
Power Delivery	85W
Input Voltage	100 - 240 AC
Input Current	2 A
Output Voltage	20V DC
Output Current	5 A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	100W

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	5%~95% RH (Non-condensing)

Physical Characteristics

Color	Black
Material	Plastic
Product Length	3.9 in [98.0 mm]
Product Width	3.6 in [91.0 mm]
Product Height	1.3 in [32.0 mm]



Weight of Product 7.1 oz [200.0 g]

Packaging Information

Package Length 6.5 in [16.5 cm]

Package Width 7.3 in [18.5 cm]

Package Height 3.7 in [95.0 mm]

Shipping (Package) Weight 2.7 lb [1.2 kg]

What's in the Box

Included in Package

- docking station
- 3.3 ft [1 m] USB-C cable
- universal power adapter (NA/JP, ANZ)
- quick-start guide

****Product appearance and specifications are subject to change without notice.***

