

USB-C Dock - Dual Monitor 1080p HDMI Laptop Docking Station - 65W Power Delivery - 1x USB-C, 3x USB-A, Ethernet - Dual Video Display USB 3.1 Gen 1 Type-C Dock - Mac & Windows

Produkt-ID: DK30CHHPD



This USB-C docking station is ideal for use in large organizations to meet widespread office productivity requirements and compatibility with all USB-C and Thunderbolt 3 laptops. The USB-C dock features support for Dual HDMI monitors, 65W Power Delivery 3.0, fast-charge, and both USB-C and USB-A peripheral ports.

The USB-C docking station adds dual HDMI monitors support to your workstation, with full high definitions resolutions of 1920x1080 or 1920x1200 at 60Hz. With more screen space, you can access multiple applications and reference material on one display while composing on the other.

The USB-A and USB-C charge ports can charge your smartphone, tablet or other USB peripherals whether you're working or away from your desk, and even if you disconnect your laptop.

Using a single cable, the dock powers and charges your laptop as you work with 65W PD for faster charging, using the 90W power adapter.

With a smaller size and extended length 3.3' (1 meter) host cable, this USB-C dock fits easily into a workspace environment. Even where desk space is limited, this dock can be mounted to the wall, monitor or underneath the desk with StarTech.com mounting brackets (SSPMSUDWM & SSPMSVESA). These mounting brackets are specifically designed for our docks and hubs to give you the customized setup you need.

Connect your devices with four USB 3.1 ports: 1x USB -C and 3x USB-A. Fast-charge your USB-C or USB-A smartphone. The dock provides a GbE port (Wake-on-LAN) and a 3.5 mm 4-position headset audio jack. It also includes a security lock slot (K-slot) to protect against theft.

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the market that works with a wide range of IT connectivity accessories. The software suite

includes:

Advanced Windows Layout Utility: To setup and save custom windows layouts.

Mac Address Pass-Through Utility: To improve network security.

USB Event Monitoring Utility: To track and log connected USB devices

Wi-Fi Auto Switch Utility: Enabling users to quickly access faster network speeds via wired LAN.

For more information and to download the StarTech.com Connectivity Tools application, please visit:
www.StarTech.com/Connectivity-Tools

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

DK30CHHPD is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **USB-C-DOCKINGSTATION MIT VOLLER AUSSTATTUNG:** Bietet einen doppelten Bildschirm mit 1080p HDMI Video, 3x USB-A, 1x USB-C, 65 W Power Delivery, Gigabit Ethernet und 3,5 mm Audio für eine effiziente USB 3.1 5Gbit/s Dockinglösung
- **UMFASSENDE GERÄTEKOMPATIBILITÄT:** Diese universelle USB-C Dockingstation ist kompatibel mit Thunderbolt 3 und kann mit HP, Lenovo, Dell, MacBook Pro und Air (2 Monitore bei Macbooks mit Intel oder Apple M1 CPU), Microsoft Surface und Chromebooks arbeiten.

- **EINFACHE EINRICHTUNG:** Dieses USB-C Dock unterstützt alle wichtigen Betriebssysteme (Windows, macOS, ChromeOS, Ubuntu) und beinhaltet DisplayLink Update Utilities für eine problemlose IT-Verwaltung
- **EINFACHE INTEGRATION AM ARBEITSPLATZ:** Dieses USB-3.0-Typ-C-Universal-Dock ist so konzipiert, dass es in jede Arbeitsumgebung passt, einschließlich gemeinsam genutzter Arbeitsbereiche oder Hotels. Es ist mit Montagelöchern, einem K-Slot und einem 1-m-USB-C-Kabel ausgestattet.
- **65W BETREIBEN & LADEN:** Dieser USB Typ-C Port Replikator betreibt und lädt während Sie arbeiten mit 65W PD für ultradünne Laptops wie Thinkpad T Series, X1 Carbon, Surface Pro7, & USB-C Chromebooks
- **CONNECTIVITY TOOLS:** Die mit diesem Gerät gelieferte Anwendung verbessert Leistung und Sicherheit und bietet MAC Address Changer, USB Event Monitoring, Fensteranordnung & Wi-Fi Auto Switch Dienstprogramme

Hardware

Garantiebestimmungen	3 Years
4K-Unterstützung	Nein
Unterstützte Displays	2
Audio	Ja
Schnittstelle	USB 3.2 Gen 1
Bustyp	USB 3.2 Gen 1
Compatible Lock Slot	Kensington Standard Slot (K-Slot)
Chipset-ID	DisplayLink - DL-3900, Realtek RTS5423, Realtek RTS5411 or RTS5411E

Leistung

Wake On Lan	Ja
Max. Datenübertragungsrate	5 Gbit/s (USB 3.0)</BR> 1 Gbit/s (Ethernet)
Max. Digitalauflösungen	Zwei HDMI-Displays: 1080p (1920 x 1080, 1920 x 1200) bei 60 Hz
Typ und Rate	USB 3.0 – 5 Gbit/s
UASP-Unterstützung	Ja

Kompatible Netzwerke 10/100/1000 Mbps

Full
Duplex-Unterstützung Nein

Steckverbinder

Steckverbindertyp(en) 1 - USB 3.2 Typ-C (24-pin, Gen 1, 5Gbit/s)

1 - USB 3.2 Typ-A (9-pin, Fast-Charge)

2 - USB Type-A (9-polig) USB 3.0 (5 Gbps)

2 - HDMI 1.4

1 - RJ-45

1 - 3.5 mm Mini-Jack (4 Position) Female

1 - USB Type-C (Fast-Charge, 24 pin) USB 3.2

Software

Betriebssystemkompatibilität Windows® 7, 8, 8.1, 10, 11

macOS 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1

Ubuntu 18.04, 20.04, 22.04, 24.04

Chrome OS™ v55+

Spezielle Hinweise/Anforderungen

Hinweis DisplayLink docking stations and video adapters support more than one external display on Apple's M1-based Mac. Requires driver installation. Please contact StarTech.com support for a recommendation based on your specific setup.

Strom

Stromversorgung Mit Netzadapter

Power Delivery 65W

Eingangsspannung 100 - 240 AC

Eingangsstrom 1.5A

Ausgangsspannung	20V DC
Ausgangsstrom	4.5A
Polarität der Mittelspitze	Positiv
Steckertyp	N
Stromverbrauch	90

Umgebungsbedingungen

Betriebstemperatur	0°C ~ 50°C
Lagertemperatur	-20°C ~ 70°C
Feuchtigkeit	0 % bis 95 % (nicht kondensierend) bei 25 °C

Physische Eigenschaften

Farbe	Schwarz & spacegrau
Produktlänge	5.9 in [15.0 cm]
Produktbreite	3.1 in [8.0 cm]
Produkthöhe	1.2 in [3.0 cm]
Produktgewicht	10.6 oz [300.0 g]

Verpackungsinformationen

Paketlänge	5.8 in [14.7 cm]
Paketbreite	9.3 in [23.5 cm]
Pakethöhe	3.4 in [8.7 cm]
Versandgewicht (Verpackung)	2.2 lb [1.0 kg]

Verpackungsinhalt

Im Paket enthalten	1 - Dockingstation
	1 - USB-C-Hostkabel (1 m)

1 - Universal Power Adapter (NA)

1 - Kurzanleitung

Garantieinformatio
nen

Warranty

3 Jahre

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.