

USB C Multiport Adapter - USB 3.1 Gen 2 10Gbps Type-C Mini Dock with 4K 60Hz HDMI/DisplayPort or 1080p VGA - 75W PD Passthrough, 3-Port USB Hub, GbE - Mobile Docking Station

Product ID: DKT31CHDVCM



This USB-C Gen 2 10Gbps multiport adapter, with backward USB-C laptop compatibility, turns your USB-C or Thunderbolt 3 Windows laptop, MacBook Pro, iPad Pro, Surface, Chromebook, or Android tablet into a workstation, anywhere you go. The USB 3.2 Gen 2 Type-C hub adapter features a unique portable, circular design and all of the essential connections

- HDMI, DisplayPort, VGA video options
- 10Gbps USB-C & USB-A peripheral ports
- Attached 24cm (10 in) USB-C host cable

This USB-C multiport adapter features HDMI, DisplayPort, and VGA ports providing you with three single video output options for your workstation setup or boardroom presentations including support for an ultra-wide monitor.

- HDMI (Up to 4K 60Hz with DP 1.4 and HDMI 2.0 HDR)
- DisplayPort (Up to 4K 60Hz with DP 1.4)
- VGA (Up to 1080p)

The USB-C travel dock features a compact circular design and an attached extended length 24cm (10 in.) host cable, accommodating a wide variety of setups. Bus-powered for most applications, there's no need to carry around a separate bulky power adapter. If extra power required, you can use your external USB-C laptop power adapter with support for up to 75W Power Delivery pass-through (15W for docking station & rest for charging).

Installation is fast and simple, with native support in most operating systems, and at only 7 ounces (198 g) and taking up less space than your smartphone, this dock easily fits in your laptop bag or briefcase with a convenient wraparound cable.

In addition to the video outputs, the portable USB-C dock gives you two 10Gbps USB-A ports and one 10Gbps USB-C port to connect the latest and legacy USB devices. The adapter also integrates a Gigabit Ethernet port to access a wired network.

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the market that works with a wide range of IT connectivity accessories. The software suite includes:

Advanced Windows Layout Utility: To setup and save custom windows layouts.

Mac Address Pass-Through Utility: To improve network security.

USB Event Monitoring Utility: To track and log connected USB devices

Wi-Fi Auto Switch Utility: Enabling users to quickly access faster network speeds via wired LAN.

For more information and to download the StarTech.com Connectivity Tools application, please visit:
www.StarTech.com/Connectivity-Tools

Certifications, Reports and Compatibility

Applications

Features

- **HIGH PERFORMANCE MINI DOCK:** Compact USB-C mobile adapter (USB 3.1 Gen 2 10Gbps); connect a single display with three video output options: DisplayPort or HDMI up to 4K 60Hz with HDR (requires DP 1.4 Alt Mode Source) or up to 1080p with VGA
 - **4K 60HZ WITH DP 1.4 ALT-MODE:** 4K 60Hz on hosts that support DP 1.4 Alt-Mode and HBR3 w/ DSC enabled laptops (min. Intel 11th Gen) or up to 4K 30Hz resolution on host devices that support DP 1.2 Alt-Mode
 - **BUILT-IN USB HUB:** This USB C multiport adapter features an integrated USB 3.2/3.1 Gen 2 hub with 2x USB-A and 1x USB-C downstream ports supporting speeds up to 10 Gbps; includes a gigabit Ethernet port
 - **EXTRA LONG CABLE:** 10" (24cm) attached cable for extended reach to reduce port strain on 2-in-1's like iPad Pro & Surface Pro 7; USB C multiport adapter with wraparound cable for office, travel & home
 - **RELIABLE PERFORMANCE:** USB bus powered or via external USB-C power adapter; 75W Power Delivery 3.0 pass through w/ 15W reserved for adapter to avoid video flickering, device dropouts or overdrawing power common in other hubs; up to 60W for laptop charging
 - **WIDE COMPATIBILITY:** A portable dock for USB-C ultrabooks, Chromebooks, tablets & Thunderbolt 3 laptops like HP, Dell, Lenovo, MacBooks (Intel processor & M1 chip), iPad Pro; works w/ Windows, macOS, iPadOS, Chrome OS, Android
 - **CONNECTIVITY TOOLS:** Provided with this device, the application improves performance and security, featuring MAC Address Changer, USB Event Monitoring, Windows Layout & Wi-Fi Auto Switch utilities
-

Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	Yes
Displays Supported	1
Ports	6
Audio	No
Interface	USB 3.2 Gen 2 - 10 Gbit/s
Bus Type	USB 3.1 Gen 2
USB Pass-Through	Yes
Industry Standards	1 Gigabit connectivity to any 1000Base-T device (IEEE802.3ab Compliant), 100 Megabit connectivity to any 100Base-TX device (IEEE802.3u Compliant), 10 Megabit connectivity to any 10Base-T device (IEEE802.3i Compliant)
Chipset ID	Genesys Logic GL9510, Genesys Logic GL3590, Realtek RTL8153, Realtek RTD2142S

Performance

Maximum Data Transfer Rate	10 Gbps
Maximum Digital Resolutions	4K 60Hz
Type and Rate	USB 3.2 Gen 2 - 10 Gbit/s

Connector(s)

Connector Type(s)	HDMI
	DisplayPort
	VGA (15 pin, High Density D-Sub)
	Ethernet Gigabit
	USB 3.1 USB Type C (10 pin, Gen 2, 10 Gbps)
	USB 3.1 USB Type-A (9 pin, Gen 2, 10 Gbps)
Host Connectors	USB 3.1 USB Type C (10 pin, Gen 2, 10 Gbps)



Software

OS Compatibility	Windows 11, Windows 10, Windows 8.1, macOS Sierra (10.12), macOS High Sierra (10.13), macOS Mojave (10.14), macOS Catalina (10.15), macOS Big Sur (11.0) macOS Monterey (12.0) Chrome OS 69.x, Android OS 9.x, iPadOS
------------------	---

Environmental

Operating Temperature	0 to 50C
Storage Temperature	-20 to 70C
Humidity	0% to 95%(non-condensing) at 25C

Physical Characteristics

Color	Black & Gray
Material	Plastic
Product Length	3.5 in [90.0 mm]
Product Width	3.5 in [90.0 mm]
Product Height	1.3 in [32.5 mm]
Weight of Product	7.1 oz [201.0 g]

Packaging Information

Package Length	5.7 in [14.5 cm]
Package Width	5.2 in [13.3 cm]
Package Height	1.5 in [37.0 mm]
Shipping (Package) Weight	9.8 oz [278.0 g]

What's in the Box

Included in Package	USB-C Multiport Adapter Quick-Start Guide
---------------------	--

**Product appearance and specifications are subject to change without notice.*

