

8" (20 cm) DMS-59 to Dual DisplayPort Adapter Cable - 4K x 2K Video - LFH DMS 59 pin (M) to 2x DisplayPort 1.2 (F) Splitter Y Cable - LFH Graphics Card to Dual DP Monitors

**Product ID:** DMSDPDP1



The DMSDPDP1 DMS-59 to Dual DisplayPort Cable allows you to split the video from a single LHF graphics card on to two DisplayPort (DP) monitors.

The DMS to DP Y cable supports high resolutions of up to 4k x 2k (3840 x 2160) with a maximum HBR2 bandwidth of 21.6 Gbps and is compatible with DMS / LFH 59 or DMS / LFH 60 graphics cards such as Matrox, NVIDIA, PNY, ATI and HP.

Backed by our Lifetime Warranty, the DMSDPDP1 is designed and constructed for maximum durability – making it a reliable and cost-effective replacement for damaged or misplaced DMS to 2x DisplayPort cables.

## Certifications, Reports and Compatibility



## Applications

- Connect two DisplayPort monitors to a single DMS / LFH 59 or DMS / LFH 60 graphics card port

## Features

- **DMS-59 TO DUAL DISPLAYPORT ADAPTER CABLE:** This 7.8 in (20 cm) DMS-59 P to 2x DP v1.2 extension cable (male to 2x female connectors) supports 4K x 2K video (3840 x 2160 60Hz), 1920 x 1200p, Full HD 1080p, 21.6 Gbps bandwidth, HBR2

- **RELIABLE DESIGN:** Durable and flexible molded PVC strain relief and jacket prevent fraying or damage due to bending or rough usage; Cost-effective replacement for damaged or misplaced DMS-59 to dual DisplayPort splitter y cables
- **QUALITY CONSTRUCTION:** 32AWG wire and EMI shielding with Aluminium foil and Braid provide superior signal integrity and reliability for higher quality video and audio; Use this DMS-59 to DisplayPort cable with DMS/LFH 59 graphics cards
- **APPLICATIONS:** Split the video from a LHF graphics card to two DP UHD/4K monitors/projectors/displays w/ this LFH cable; Ideal for home/office/classroom works w/ professional workstations with ATI Radeon X1300, NVIDIA Quadro NVS 440, Matrox Xenia, HP, PNY
- **SPECS:** 7.8 inch (20 cm) Black Dual Monitor Solution (DMS), 59 pins Male DMS 59P Plug to 2x Standard DP Female adapter cable 32 AWG, 0.2"(5.5mm) Outer Diameter PVC cable jacket EMI Shield: Aluminium foil with Braid

---

#### Hardware

|                       |                                |
|-----------------------|--------------------------------|
| Warranty              | Lifetime                       |
| Connector Plating     | Nickel                         |
| Cable Jacket Material | PVC - Polyvinyl Chloride       |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

---

#### Connector(s)

|             |                          |
|-------------|--------------------------|
| Connector A | 1 - DMS-59 (59 pin)      |
| Connector B | 2 - DisplayPort (20 pin) |

---

#### Physical Characteristics

|                   |                   |
|-------------------|-------------------|
| Color             | Black             |
| Connector Style   | Straight          |
| Wire Gauge        | 32 AWG            |
| Cable Length      | 8.0 in [203.2 mm] |
| Product Length    | 8.0 in [203.2 mm] |
| Product Width     | 1.6 in [41.0 mm]  |
| Product Height    | 0.6 in [1.5 cm]   |
| Weight of Product | 2.8 oz [79.0 g]   |

---

**Packaging  
Information**

|                              |                   |
|------------------------------|-------------------|
| Package Quantity             | 1                 |
| Package Length               | 11.4 in [29.0 cm] |
| Package Width                | 5.7 in [14.5 cm]  |
| Package Height               | 0.7 in [17.0 mm]  |
| Shipping (Package)<br>Weight | 3.0 oz [86.0 g]   |

---

**What's in the Box**

|                     |                                                             |
|---------------------|-------------------------------------------------------------|
| Included in Package | 1 - 8in LFH 59 Male to Dual Female DisplayPort DMS 59 Cable |
|---------------------|-------------------------------------------------------------|

---

***\*Product appearance and specifications are subject to change without notice.***