

## 10 ft DisplayPort to VGA Adapter Converter Cable – DP to VGA 1920x1200 - Black

### Product ID: DP2VGAMM10B

The DP2VGAMM10B 10ft active DisplayPort to VGA converter cable lets you connect your DisplayPort-equipped desktop or laptop directly to a VGA monitor or projector with no additional adapters or cables required -- a cost-effective solution for enabling your new Mini DisplayPort computer to work with an older VGA monitor or projector.

Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a DisplayPort video source to VGA without sacrificing video quality.

The DP2VGAMM10B is backed by a 3-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Connect your existing VGA display device (monitor, projector) to a DisplayPort output device (Desktop, Laptop computer)
- Use your VGA monitor as a secondary display, connected to a DisplayPort output
- Connect a DisplayPort computer to a VGA projector for presentations or meetings in a boardroom or auditorium setting

### Features

- Active DisplayPort to VGA conversion
- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- Plug-and-Play Installation

---

#### Hardware

|                           |                   |
|---------------------------|-------------------|
| Warranty                  | 3 Years           |
| Active or Passive Adapter | Active            |
| AV Input                  | DisplayPort - 1.2 |
| AV Output                 | VGA               |
| Audio                     | No                |
| Chipset ID                | Analogix - 9832   |

---

## Performance

|                             |                            |
|-----------------------------|----------------------------|
| Maximum Cable Length        | 10.0 ft [3.0 m]            |
| Maximum Analog Resolutions  | 1920x1200 / 1080p (Output) |
| Maximum Digital Resolutions | 1920x1200 / 1080p (Input)  |
| Audio Specifications        | VGA - No Audio Support     |
| MTBF                        | 1,449,804 hours            |

---

## Connector(s)

|             |                                  |
|-------------|----------------------------------|
| Connector A | DisplayPort (20 pin)             |
| Connector B | VGA (15 pin, High Density D-Sub) |

---

## Environmental

|                       |                           |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 60C (32F to 140F)   |
| Storage Temperature   | -10C to 70C (14F to 158F) |
| Humidity              | 40%-85%RH                 |

---

## Physical Characteristics

|                   |                   |
|-------------------|-------------------|
| Color             | Black             |
| Cable Length      | 10.0 ft [3.0 m]   |
| Product Length    | 36.0 in [91.5 cm] |
| Product Width     | 1.3 in [33 mm]    |
| Product Height    | 0.6 in [15 mm]    |
| Weight of Product | 5.2 oz [148.5 g]  |

---

## Packaging Information

|                           |                  |
|---------------------------|------------------|
| Package Length            | 8.7 in [22.2 cm] |
| Package Width             | 7.8 in [19.7 cm] |
| Package Height            | 0.8 in [20 mm]   |
| Shipping (Package) Weight | 5.3 oz [150 g]   |



---

**What's in the  
Box**

|                     |                                  |
|---------------------|----------------------------------|
| Included in Package | DisplayPort to VGA Adapter Cable |
|---------------------|----------------------------------|

---

***\*Product appearance and specifications are subject to change without notice.***

