

6 ft DisplayPort to VGA Cable - M/M

Product ID: DP2VGAMM6



The DP2VGAMM6 6ft DisplayPort to VGA (M-M) Cable lets you connect a VGA capable display to a DisplayPort video card/source. The cable provides a connection distance of 6 feet and features a male VGA connector and a male DisplayPort connector.

The DisplayPort to VGA adapter cable supports high bandwidth video transmissions, easily delivering monitor resolutions up to 1920x1200 or HDTV resolutions up to 1080p - allowing you to take full advantage of your VGA display, while using a cutting edge DisplayPort video source.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Keep your existing VGA display to use with newer DisplayPort monitors
- The DisplayPort to VGA cable allows for an easy and hassle free connection to any VGA monitor or projector

Features

- All-in-one cable design
- Supports PC resolutions up to 1920x1200 (HDTV - 1080p)
- No software or drivers required

Hardware

Warranty

2 Years

Active or Passive Adapter	Active
AV Input	DisplayPort - 1.2
AV Output	VGA
Audio	No
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance	Maximum Cable Length	6.0 ft [1.8 m]
	Maximum Digital Resolutions	1920x1200 / 1080p
	Audio Specifications	VGA - No Audio Support

Connector(s)	Connector A	DisplayPort (20 pin)
	Connector B	VGA (15 pin, High Density D-Sub)

Environmental	Operating Temperature	0C to 45C (32F to 113F)
	Storage Temperature	-10C to 70C (14F to 158F)
	Humidity	10%-85%RH

Physical Characteristics	Color	Black
	Cable Length	6.0 ft [1.8 m]
	Product Length	6.0 ft [1.8 m]
	Product Width	1.4 in [35.000 mm]
	Product Height	5.6 ft [1.7 m]
	Weight of Product	3.7 oz [106.000 g]

Packaging Information	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2.0 cm]
	Package Height	0.0 in [0.100 mm]
	Shipping (Package) Weight	4.0 oz [114.000 g]

What's in the Box	Included in Package	6 ft DisplayPort to VGA Cable - M/M
--------------------------	---------------------	-------------------------------------

**Product appearance and specifications are subject to change without notice.*