

## 6 ft DisplayPort Video Extension Cable - M/F

Product ID: DPEXT6L



The DPEXT6L 6-foot, DisplayPort Video Extension Cable adds an extra 6ft to any DisplayPort cable.

The extension cable features latching, gold-plated connectors for superior conductivity and is backed by our Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Extend your DisplayPort interface by 6ft

### Features

- Molded latching connectors with strain relief
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
- Aluminum-Mylar Foil with Braided Shielding

Hardware	Warranty	Lifetime
	Number of Conductors	20
	Connector Plating	Gold
	Cable Jacket Material	PVC - Polyvinyl Chloride

	Cable Shield Material	Aluminum-Mylar Foil with Braid
	Fire Rating	CMG Rated (General Purpose)
<b>Connector(s)</b>	Connector A	DisplayPort (20 pin)
	Connector B	DisplayPort (20 pin)
<b>Environmental</b>	Operating Temperature	-20C to 80C (-4F to 158F)
	Storage Temperature	-25C to 85C (-13F to 185F)
	Humidity	40%-70%RH
<b>Physical Characteristics</b>	Color	Black
	Wire Gauge	28 AWG
	Cable Length	6.0 ft [1.8 m]
	Product Length	6.0 ft [1.8 m]
	Product Width	0.8 in [20.9 mm]
	Product Height	0.5 in [12.6 mm]
	Weight of Product	3.2 oz [91.000 g]
<b>Packaging Information</b>	Package Length	8.7 in [2.2 cm]
	Package Width	0.8 in [20.000 mm]
	Package Height	7.9 in [2.0 cm]
	Shipping (Package) Weight	3.4 oz [96.000 g]
<b>What's in the Box</b>	Included in Package	6 ft DisplayPort Video Extension Cable - M/F

*\*Product appearance and specifications are subject to change without notice.*

