

6in DisplayPort Port Saver Cable – M/F

Produkt ID: DPEXTAA6IN



The DPEXTAA6IN 6-inch DisplayPort Port Saver Cable/coupler avoids expensive repairs to a computer or display. It does this by extending the port by 6in, thereby eliminating the weight and stress that would typically be placed on the port by a DisplayPort cable. This is especially useful in an environment where cables are unplugged and re-inserted frequently.

Certifikat, rapporter och kompatibilitet

Användning

- Protect the on-board DisplayPort interface from damage cause by frequent connect/disconnects
- Allows supported Displayport devices to draw power from the host device

Funktioner

- Molded latching connectors with strain relief
- Includes all 20 DisplayPort pins to support Multi-Mode DisplayPort devices
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP

Hårdvara

Garantipolicy

Lifetime

Antal ledare	20
Kontaktplätering	Guld
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning

Kontakt(er)

Connector A	DisplayPort (20-stifts)
Connector B	DisplayPort (20-stifts)

Utseende

Färg	Svart
Tråddimension	28 AWG
Maximal kontaktdimension	0.8 in [20.4 mm]
Kabellängd	6.0 in [15.2 cm]
Yttre kabeldiameter	0.3 in [7.3 mm]
Produktvikt	1.3 oz [38 g]

Förpackning

Package Length	4.7 in [11.9 cm]
Package Width	0.7 in [19 mm]
Package Height	8.4 in [21.3 cm]
Fraktvikt (förpackning)	2.5 oz [70 g]

Vad det är i lådan

Ingår i paketet	6in DisplayPort port extension
-----------------	--------------------------------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

