

## 3ft DisplayPort Panel Mount Cable - F/M

Produkt ID: DPPNLFM3



This 3ft panel mount DisplayPort cable features a DisplayPort male connector on one end, and a DisplayPort panel mount (female) molded connector on the other, providing a well-secured, easy to access DisplayPort connection on any machine port or faceplate.

Backed by StarTech.com's Lifetime Warranty

## Certifikat, rapporter och kompatibilitet

### Användning

- Extend your DisplayPort interface and allow you screw mount it to a panel

### Funktioner

- Latched connectors to reduce accidental disconnects

---

#### Hårdvara

Garantipolicy	Lifetime
Antal ledare	19
Kontaktplätering	Nickel

Kabelmanteltyp	PVC - Polyvinyl Chloride
Brandteknisk klass	CMG-klass (General Purpose)

---

Kontakt(er)

Connector A	DisplayPort (20-stifts)
Connector B	DisplayPort (20-stifts)

---

Miljö

Drifttemperatur	-20°C to 80°C
Förvaringstemperatur	-20°C to 80°C
Luftfuktighet	15 till 65 %

---

Utseende

Färg	Svart
Tråddimension	28 AWG
Kabellängd	36.0 in [91.4 cm]
Yttre kabelldiameter	0.3 in [7.3 mm]
Produktlängd	36.0 in [91.4 cm]
Produktvikt	3.3 oz [94 g]

---

Förpackning

Package Length	7.9 in [20 cm]
Package Width	0.0 in [0.1 mm]
Package Height	8.3 in [21 cm]
Fraktvikt (förpackning)	3.3 oz [94 g]

---

Vad det är i lådan

Ingår i paketet	3ft. Panel Mount DisplayPort Cable
-----------------	------------------------------------

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.