

3ft DisplayPort Panel Mount Cable - F/M

Product ID: DPPNLFM3



This 3ft panel mount DisplayPort cable features a DisplayPort male connector on one end, and a DisplayPort panel mount (female) molded connector on the other, providing a well-secured, easy to access DisplayPort connection on any machine port or faceplate.

Backed by StarTech.com's Lifetime Warranty

Certifications, Reports and Compatibility

Applications

- Extend your DisplayPort interface and allow you screw mount it to a panel

Features

- Latched connectors to reduce accidental disconnects

Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride

Fire Rating CMG Rated (General Purpose)

Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	DisplayPort (20 pin)

Environmental

Operating Temperature	-20C to 80C
Storage Temperature	-20C to 80C
Humidity	15 to 65%

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	36.0 in [91.4 cm]
Cable OD	0.3 in [7.3 mm]
Product Length	36.0 in [91.4 cm]
Weight of Product	3.3 oz [94 g]

Packaging Information

Package Length	7.9 in [20 cm]
Package Width	0.0 in [0.1 mm]
Package Height	8.3 in [21 cm]
Shipping (Package) Weight	3.3 oz [94 g]

What's in the Box

Included in Package	3ft. Panel Mount DisplayPort Cable
---------------------	------------------------------------

****Product appearance and specifications are subject to change without notice.***

