

3ft (91cm) Panel Mount DisplayPort Cable - 4K x 2K - DisplayPort 1.2 Extension Cable Male to Female - DP Video Extender Cord with Panel Mount DP Connector - DP Monitor Cable

Produkt ID: DPPNLFM3PW



The DPPNLFM3PW 3ft DisplayPort Extension Panel Mount Cable features one DP male connector and one panel mount DP female connector, providing a well-secured, easy to access DisplayPort connection on your PC or faceplate, and allowing you to customize your systems to suit your needs. If power is required, the DisplayPort Cable uses all 20 pins and can deliver power accordingly.

The DPPNLFM3PW is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifikat, rapporter och kompatibilitet



Användning

- Extend your DisplayPort interface and screw mount it to a panel

Funktioner

- PANEL MOUNT DISPLAYPORT CABLE: 3ft (91 cm) DisplayPort v1.2 male to female extender cable; 4K x 2K (3840x2400p 60Hz), 21.6 Gbps bandwidth , HBR2, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (2560x1600p 120Hz)

- **RELIABLE DESIGN:** Durable molded female connector with two 4-40 screws to secure on to a machine faceplate/port; Flexible PVC strain relief & jacket prevent fraying/damage due to bending/rough usage; Latching connector prevents accidental disconnection
- **QUALITY CONSTRUCTION:** 28AWG wire with gold-plated pins for improved signal integrity and reliability; DisplayPort panel mount cable / video cord has superior EMI shielding with double sided copper foil to provide higher quality video and audio
- **APPLICATIONS:** Add extra 3ft to your DP cables; DisplayPort extension cable for home/offices/boardrooms/classrooms; works with your professional workstations with FirePro™ S9000/7000, W8100/7100 graphic cards; Use w/ 1080p/UHD/4K monitors/projector/display
- **SPECS:** 3 foot (91 cm) | Black | DisplayPort 1.2 | DP Latching Male to DP Female (panel mountable w/ 2x 4-40 UNC screws) | 28 AWG | PVC cable jacket, ABS connector shell | Shield: Double sided copper foil | Backward compatible w/ DP1.1 | Lifetime Warranty

Hårdvara

Garantipolicy	Lifetime
Antal ledare	20
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Brandteknisk klass	CMG-klass (General Purpose)

Prestanda

Maximal digital upplösning	4k x 2k (4096 x 2160) vid 60 Hz
----------------------------	---------------------------------

Kontakt(er)

Connector A	1 - DisplayPort (20-stifts)
Connector B	1 - DisplayPort (20-stifts)

Miljö

Drifttemperatur	-10°C to 40°C (14°F to 104°F)
Förvaringstemperatur	-10°C to 80°C (14°F to 176°F)
Luftfuktighet	0 to 85% RH

Utseende

Färg	Svart
------	-------

Tråddimension	28 AWG
Kabellängd	3.0 ft [0.9 m]
Produktlängd	36.2 in [92.0 cm]
Produktbredd	1.3 in [3.4 cm]
Produkthöjd	0.5 in [1.2 cm]
Produktvikt	2.5 oz [72.0 g]

Förpackning

Förpackningsantal	1
Paketets längd	5.8 in [14.7 cm]
Paketets bredd	4.9 in [12.5 cm]
Paketets höjd	1.2 in [3.0 cm]
Fraktvikt (förpackning)	2.8 oz [78.0 g]

Vad det är i lådan

Ingår i paketet	1 - 3ft DisplayPort Extension Panel Mount Cable
-----------------	---

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.