

3ft (1m) Panel Mount DisplayPort Cable - 4K x 2K - DisplayPort 1.2 Extension Cable Male to Female
- DP Video Extender Cord with Panel Mount DP Connector - DP Monitor Cable

Product ID: DPPNLFM3PW



The DPPNLFM3PW 3ft DisplayPort Extension Panel Mount Cable features one DP male connector and one panel mount DP female connector, providing a well-secured, easy to access DisplayPort connection on your PC or faceplate, and allowing you to customize your systems to suit your needs. If power is required, the DisplayPort Cable uses all 20 pins and can deliver power accordingly.

The DPPNLFM3PW is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Extend your DisplayPort interface and screw mount it to a panel

Features

- **PANEL MOUNT DISPLAYPORT CABLE:** 3ft (91 cm) DisplayPort v1.2 male to female extender cable; 4K x 2K (3840x2400p 60Hz), 21.6 Gbps bandwidth, HBR2, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (2560x1600p 120Hz)
- **RELIABLE DESIGN:** Durable molded female connector with two 4-40 screws to secure on to a machine faceplate/port; Flexible PVC strain relief & jacket prevent fraying/damage due to bending/rough usage; Latching

connector prevents accidental disconnection

- **QUALITY CONSTRUCTION:** 28AWG wire with gold-plated pins for improved signal integrity and reliability; DisplayPort panel mount cable / video cord has superior EMI shielding with double sided copper foil to provide higher quality video and audio
- **APPLICATIONS:** Add extra 3ft to your DP cables; DisplayPort extension cable for home/offices/boardrooms/classrooms; works with your professional workstations with FirePro S9000/7000, W8100/7100 graphic cards; Use w/ 1080p/UHD/4K monitors/projector/display
- **SPECS:** 3' (0.91m) Black DisplayPort 1.2 DP Latching Male to DP Female (panel mountable w/ 2x 4-40 UNC screws) 28 AWG PVC cable jacket, ABS connector shell Shield: Double sided copper foil Backward compatible w/ DP1.1 Lifetime Warranty

Hardware

| | |
|-----------------------|-----------------------------|
| Warranty | Lifetime |
| Number of Conductors | 20 |
| Connector Plating | Nickel |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Fire Rating | CMG Rated (General Purpose) |

Performance

| | |
|-----------------------------|------------------------------|
| Maximum Digital Resolutions | 4k x 2k (4096 x 2160) @ 60Hz |
|-----------------------------|------------------------------|

Connector(s)

| | |
|-------------|--------------------------|
| Connector A | 1 - DisplayPort (20 pin) |
| Connector B | 1 - DisplayPort (20 pin) |

Environmental

| | |
|-----------------------|---------------------------|
| Operating Temperature | -10C to 40C (14F to 104F) |
| Storage Temperature | -10C to 80C (14F to 176F) |
| Humidity | 0 to 85% RH |

Physical Characteristics

| | |
|--------------|----------------|
| Color | Black |
| Wire Gauge | 28 AWG |
| Cable Length | 3.0 ft [0.9 m] |

| | |
|-------------------|------------------|
| Product Length | 3.0 ft [0.9 m] |
| Product Width | 1.3 in [34.0 mm] |
| Product Height | 0.5 in [1.2 cm] |
| Weight of Product | 2.9 oz [83.0 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Quantity | 1 |
| Package Length | 8.7 in [22.0 cm] |
| Package Width | 7.9 in [20.0 cm] |
| Package Height | 1.0 in [25.0 mm] |
| Shipping (Package) Weight | 0.2 lb [0.1 kg] |

What's in the Box

| | |
|---------------------|--|
| Included in Package | 1 - 3ft DisplayPort Panel Mount Cable with Power |
|---------------------|--|

**Product appearance and specifications are subject to change without notice.*