

## 8 Port VGA over Cat5 Digital Signage Broadcaster with RS232 & Audio

Productcode: DS128



StarTech.com's DS Series Cat5 Digital Signage Broadcaster with RS232 Serial and Audio offers a comprehensive audio and video extension system, with the added benefit of serial control!

Compatible with virtually any VGA-capable PC or Digital Signage media player, the DS128 VGA Splitter lets you deliver VGA video as well as the accompanying audio and serial control signals to the connected Cat5 VGA Receivers (DSRXL - purchased separately), all through one Cat5 cable.

Comprised of this unit (DS128) and the corresponding receivers, our DS Series offers several unique features compared to our other VGA Extenders, including the ability to extend RS-232 serial signals from the source to each display for controlling the displays as well as Java Client Management Software (DSNet Manager) that simplifies adjusting the settings for each receiver and display. The software can be controlled via an Ethernet port on a PC/Media Player or on a LAN (Local Area Network).

Ensuring not only a simple and cost-effective way to extend and control VGA video and the corresponding audio, the DS series (DS128 and DSRXL) also maintains exceptional, high quality video, up to 1600x1200 over a 100m connection. For further extension, you can daisy chain up to five receivers, for a maximum distance of 300m.

### Certificaties, rapporten en compatibiliteit

### Toepassingen

- Use digital signage to catch the attention of your audience and deliver up to date content the way you want it to be seen and heard.

- The DS Series can be used in education, healthcare, retail, hospitality, and other environments.
- Broadcast up to 80 displays when daisy chaining receivers. Deliver a VGA, audio and serial signal to each display along with the DSRXL receivers. With RS-232 controls you can control displays from the PC or media player.

## Eigenschappen

- DS Series 8 Port Broadcaster is able to send out VGA, Audio, and RS-232 signals to the DSRXL receiver
- Supports resolutions up to 1600x1200 at 100m / 300ft distance. Ability to go up to a total maximum 300m / 900ft when daisy chaining a maximum of five DSRXL receivers
- Included DSNet Manager JAVA based software puts you in control. Software allows access to each receiver to configure system, image quality, power on/off receivers, and turn video or audio off.

---

### Hardware

|                        |                                       |
|------------------------|---------------------------------------|
| Garantiebeleid         | 2 Years                               |
| Poorten                | 8                                     |
| Bekabeling             | Cat5 UTP                              |
| Audio                  | Ja                                    |
| Rack-monteerbaar       | Ja                                    |
| Industriestandaarden   | DDC/EDID Emulation for port 1 monitor |
| Op elkaar aansluitbaar | Ja                                    |

---

### Prestaties

|                             |  |
|-----------------------------|--|
| Maximale kabellengte        | 32.8 ft [10 m]   |
| Max. afstand                | 300 m / 950 ft   |
| Maximale analoge resoluties | 1600x1200  |
| Ondersteunde resoluties     | 1600x1200 @ 100m / 330ft<br>1280 x 1024 @ 300m / 950ft |
| Ondersteuning breedbeeld:   | Ja   |



---

#### Connector(en)

|                            |  |
|----------------------------|--|
| Connectoren lokale eenheid | RJ-45                                    |
|                            | VGA (15-polig, D-Sub met hoge dichtheid) |
|                            | VGA (15-polig, D-Sub met hoge dichtheid) |
|                            | 3,5 mm mini-jack (3 standen)             |
|                            | DB-9 (9-polig, D-Sub)                    |
|                            | DB-9 (9-polig, D-Sub)                    |

---

#### Speciale opmerkingen / vereisten

|                            |   |
|----------------------------|---|
| Systeem- en kabelvereisten | One <a href="http://www.startech.com/item/DSRXL">Cat5 VGA Receiver</a> (DSRXL) per monitor you are connecting |
| Notitie                    | Up to 5 receiver units can be daisy-chained from the broadcaster unit extending to a maximum distance of 300m |

---

#### Indicatoren

|                 |   |
|-----------------|---|
| LED-indicatoren | Power (Red)                             |
|                 | Link (Green) - LAN link status          |
|                 | 10/100 (Red) - LAN speed                |
|                 | Receiver (Green) - Receiver link status |

---

#### Voeding

|                           |                               |
|---------------------------|-------------------------------|
| Inclusief voedingsadapter | Inclusief wisselstroomadapter |
| Uitgangsspanning          | 5 DC                          |
| Uitgangsstroom            | 2A                            |
| Polariteit pin midden     | Positief                      |
| Stekkertype               | M                             |
| Vermogensopname           | 10                            |

---

#### Gebruiksomge



ving

|                     |                               |
|---------------------|-------------------------------|
| Bedrijfstemperatuur | 0°C to 40°C (32°F to 104°F)   |
| Opslagtemperatuur   | -20°C to 60°C (-4°F to 140°F) |
| Vochtigheid         | 0~90% RH                      |

---

Fysieke eigenschappen

|                 |                   |
|-----------------|-------------------|
| Kleur           | Zwart             |
| Type behuizing  | Staal             |
| Lengte product  | 11.8 in [30.0 cm] |
| Breedte product | 6.3 in [16.0 cm]  |
| Hoogte product  | 1.6 in [40.0 mm]  |
| Gewicht product | 3.1 lb [1.4 kg]   |

---

Verpakkingsinformatie

|                          |                   |
|--------------------------|-------------------|
| Package Length           | 12.6 in [32.0 cm] |
| Package Width            | 9.8 in [24.9 cm]  |
| Package Height           | 6.8 in [17.2 cm]  |
| Verzendgewicht (verpakt) | 5.9 lb [2.7 kg]   |

---

Wat wordt er meegeleverd

|             |   |
|-------------|---|
| Meegeleverd | <ul style="list-style-type: none"> <li>Instruction Manual</li> <li>Digital Signage 8 Port Transmitter</li> <li>Universal Power Adapter (NA/UK/EU/AUS)</li> <li>DSNet Manager Software CD</li> <li>Rack Mounting Brackets (w/ Screws)</li> <li>VGA Cable</li> <li>3.5mm Audio Cable</li> </ul> |
|-------------|---|



---

\* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

