

Digital Signage Display Stand - Black - Locking

Product ID: DSIGNAGESTND



The digital signage stand provides a convenient and cost-effective way to communicate with clients. Engineered with a sleek and sturdy design, the portrait kiosk enclosure provides a secure mount for a 45" to 55" TV (with maximum weight of 176 lb./80 kg) that will attract and captivate passersby.

The digital signage mount features durable construction which makes it ideal for commercial use, in environments such as trade shows and retail establishments. While many kiosks have a built-in display, the LCD advertising stand display allows you to repurpose an existing display or one of your choice. Built-in cable management keeps your cables organized and hidden from view. The digital signage kiosk enclosure features a lockable cabinet for installing your computer, media player or video extender.

The flat TV stand features a solid base that provides the display with stability, perfect for use in areas with heavy traffic. The base of the touch screen kiosk stand is designed to be bolted to the floor to provide greater stability than freestanding display kiosks.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

This DSIGNAGESTND is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Keep guests informed in hotels, restaurants, train stations, or airports
- Create an interactive display or map for wayfinding

- Perfect for advertising with dynamically updated content on your display

Features

- Built-in cabinet with lock protects your video equipment from theft and tampering
- Heavy-duty steel TV mount supports up to 175 lb. (80 kg)
- Hook-and-mount design for easy setup with VESA compliant TVs
- Integrated cable management allows for clean installation
- **DISPLAY COMPATIBILITY:** Universal LCD/LED television mount supports LG, Samsung, Sony, Sharp, others (screws/spacers incl) & VESA bracket hole patterns 200x200, 200x300, 200x400, 300x200, 300x300, 400x200, 400x300, 400x400, 600x200, 600x300, 600x400

Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
Tools Included	Yes
Articulating	No
# of Displays Supported	1
Orientation	Vertical
Mounting Options	Desktop Stand
VESA Hole Pattern(s)	200x200 mm
	200x300 mm
	200x400 mm
	300x200 mm
	300x300 mm
	400x200 mm
	400x300 mm
	400x400 mm

600X200 mm

600x300 mm

600x400 mm

Performance

Weight Capacity (Per Display)	176.8 lb [80 kg]
Minimum Display Size	45"
Maximum Display Size	55"
Fits Curved Display	No
Anti-theft	Yes

Physical Characteristics

Product Length	37.8 in [96.0 cm]
Product Width	13.8 in [35.0 cm]
Product Height	6.4 ft [1.9 m]
Weight of Product	88.6 lb [40.1 kg]

Packaging Information

Package Length	17.1 in [43.5 cm]
Package Width	4.8 ft [1.5 m]
Package Height	10.6 in [27.0 cm]
Shipping (Package) Weight	97.5 lb [44.1 kg]

What's in the Box

Included in Package	Lower Base Board
	Lower Columns
	Lower Column Caps
	Cabinet



Upper Base Board

Upper Column, Left

Upper Column, Right

End Caps

Cross Bars

TV Brackets

Cable Bracket

Locking Brackets

Cable Clips

Screw Caps

M10 x 25 Screws

M6 x 12 Screws

M8 x 60 Screws

M8 Nuts

M6 x 15 Screws

M6 x 35 Screws

M4 x 6 Screws

Screws

Cable Ties

4mm Hex Key

6mm Hex Key

5mm Hex Key

M6/M8 Wrench

M5 x 14 Screws

M6 x 14 Screws

M8 x 30 Screws



M8 x 50 Screws

Rectangular Washers

Small Spacers

Large Spacers

Floor Anchor

Instruction Manual

****Product appearance and specifications are subject to change without notice.***

