

## VGA over Cat5 Digital Signage Receiver for DS128 with RS232 & Audio

Productcode: DSRXL



StarTech.com's DS Series Digital Signage Broadcaster VGA Cat5 Receiver offers a comprehensive audio and video extension system, with the added benefit of serial control!

The DSRXL VGA Receiver(s) can be installed at the destination points, allowing you to distribute VGA video as well as the accompanying audio and serial control signals from the connected Serial, Audio and VGA Cat5 Digital Signage Broadcaster (DS128 - purchased separately), all over one Cat5 cable.

Ensuring not only a simple and cost-effective way to extend and control VGA video and the corresponding audio, the DS series (DS128 and DSRXL) also maintains exceptional, high quality video, up to 1600x1200 over a 100m connection. For further extension, you can daisy chain up to five receivers, for a maximum distance of 300m.

## Certificaties, rapporten en compatibiliteit

### Toepassingen

- Use digital signage to catch the attention of your audience and deliver up to date content the way you want it to be seen and heard.
- The DS Series can be used in education, health care, retail, hospitality, and other environments.
- Broadcast up to 80 displays when daisy chaining receivers. Deliver a VGA, audio and serial signal to each display along with the DSRXL receivers. With RS-232 controls you can control displays from the PC or media player.

## Eigenschappen

- Receiver supports VGA, audio, and RS-232 serial signals when used with DS Series DS128 8 Port Transmitter
- DSNet Manager JAVA based software puts you in control. Software allows access to each receiver to configure system, image quality, power on/off receivers, and turn video or audio off.
- Supports resolutions up to 1600x1200 at 100m / 300ft distance. Ability to go up to a total maximum 300m / 900ft when daisy chaining a maximum of five DSRXL receivers.
- Easily scalable system allows up to 80 displays to be connected using the DS Series eight port transmitter and DSRXL receivers.

---

### Hardware

Garantiebeleid	2 Years
Poorten	1
Bekabeling	Cat5 UTP
Audio	Ja
Rack-monteerbaar	Ja
Industriestandaarden	DDC/EDID Emulation for port 1 monitor
Op elkaar aansluitbaar	Ja

---

### Prestaties

Maximale kabellengte	32.8 ft [10 m]
Max. afstand	300 m / 950 ft
Maximale analoge resoluties	1600x1200
Ondersteunde resoluties	1600x1200 @ 100m(330ft) 1280x1024 @ 300m(950ft)
Ondersteuning breedbeeld:	Ja
Audiospecificaties	Two channel stereo audio supported

---

### Connector(en)



Aansluitingen externe eenheid	3,5 mm mini-jack (3 standen)
	DB-9 (9-polig, D-Sub)
	RJ-45
	VGA (15-polig, D-Sub met hoge dichtheid)

---

Speciale opmerkingen / vereisten

Notitie	Up to 5 receiver units can be daisy-chained from the broadcaster unit extending to a maximum distance of 300m
---------	---

---

Voeding

Inclusief voedingsadapter	Inclusief wisselstroomadapter
Uitgangsspanning	5 DC
Uitgangsstroom	2A
Polariteit pin midden	Positief
Vermogensopname	10

---

Gebruiksomgeving

Bedrijfstemperatuur	0°C to 40°C (32°F to 104°F)
Opslagtemperatuur	-20°C to 60°C (-4°F to 140°F)
Vochtigheid	0~90% RH

---

Fysieke eigenschappen

Kleur	Zwart
Type behuizing	Staal
Lengte product	5.3 in [13.5 cm]
Breedte product	5.2 in [13.2 cm]
Hoogte product	1.0 in [26 mm]



Gewicht product 18.6 oz [526 g]

---

Verpakkingsinformatie

Package Length 8.1 in [20.6 cm]  
Package Width 5.7 in [14.5 cm]  
Package Height 6.9 in [17.6 cm]  
Verzendgewicht (verpakt) 2.3 lb [1.0 kg]

---

Wat wordt er meegeleverd

Meegeleverd  
Digital Signage Receiver  
Mounting Brackets w/ Screws  
Universal Power Adapter (NA/UK/EU/AUS)  
Instruction Manual

---

\* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

