

VGA over Cat5 Digital Signage Receiver for DS128 with RS232 & Audio

Produkt ID: DSRXL



StarTech.com's DS Series Digital Signage Broadcaster VGA Cat5 Receiver offers a comprehensive audio and video extension system, with the added benefit of serial control!

The DSRXL VGA Receiver(s) can be installed at the destination points, allowing you to distribute VGA video as well as the accompanying audio and serial control signals from the connected Serial, Audio and VGA Cat5 Digital Signage Broadcaster (DS128 - purchased separately), all over one Cat5 cable.

Ensuring not only a simple and cost-effective way to extend and control VGA video and the corresponding audio, the DS series (DS128 and DSRXL) also maintains exceptional, high quality video, up to 1600x1200 over a 100m connection. For further extension, you can daisy chain up to five receivers, for a maximum distance of 300m.

Certifikat, rapporter och kompatibilitet



Användning

- Use digital signage to catch the attention of your audience and deliver up to date content the way you want it to be seen and heard.
- The DS Series can be used in education, health care, retail, hospitality, and other environments.
- Broadcast up to 80 displays when daisy chaining receivers. Deliver a VGA, audio and serial signal to

each display along with the DSRXL receivers. With RS-232 controls you can control displays from the PC or media player.

Funktioner

- Receiver supports VGA, audio, and RS-232 serial signals when used with DS Series DS128 8 Port Transmitter
- DSNet Manager JAVA based software puts you in control. Software allows access to each receiver to configure system, image quality, power on/off receivers, and turn video or audio off.
- Supports resolutions up to 1600x1200 at 100m / 300ft distance. Ability to go up to a total maximum 300m / 900ft when daisy chaining a maximum of five DSRXL receivers.
- Easily scalable system allows up to 80 displays to be connected using the DS Series eight port transmitter and DSRXL receivers.

Hårdvara

Garantipolicy	2 Years
Portar	1
Kablage	Cat 5 UTP
Audio	Ja
Hyllmonterbar	Ja
Industristandarder	DDC/EDID Emulation for port 1 monitor
Kedjekoppling	Ja

Prestanda

Maximal kabellängd	32.8 ft [10 m]
Maximalt avstånd	300m [984ft]
Maximal analog upplösning	1600x1200
Stödda upplösningar	1600x1200 @ 100m(330ft) 1280x1024 @ 300m(950ft)
Stöd för widescreen	Ja

Audio-specifikationer		Two channel stereo audio supported
Kontakt(er)	Fjärrenhetskontakter	2 - 3.5 mm minijack (3-polig)
		2 - DB-9 (9-stifts, D-Sub)
		2 - RJ-45
		2 - VGA (15-stifts, High Density D-Sub)
Särskilda anmärkningar/krav	Obs.	Up to 5 receiver units can be daisy-chained from the broadcaster unit extending to a maximum distance of 300m
Ström	Strömkälla	AC-adapter medföljer
	Utspanning	5 DC
	Utström	2A
	Polaritet på mittpol	Positiv
	Strömförbrukning	10
Miljö	Drifttemperatur	0°C to 40°C (32°F to 104°F)
	Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
	Luftfuktighet	0~90% RH
Utseende	Färg	Svart
	Kabinetttyp	Stål
	Produktlängd	5.3 in [13.5 cm]
	Produktbredd	5.2 in [13.2 cm]
	Produkthöjd	1.0 in [2.6 cm]

	Produktvikt	1.2 lb [0.5 kg]
Förpackning		
	Förpackningsantal	1
	Paketets längd	8.1 in [20.6 cm]
	Paketets bredd	5.7 in [14.5 cm]
	Paketets höjd	6.9 in [17.6 cm]
	Fraktvikt (förpackning)	2.3 lb [1.0 kg]
Vad det är i lådan		
	Ingår i paketet	1 - Digital Signage Receiver
		2 - Mounting Brackets w/ Screws
		1 - Universal Power Adapter (NA/UK/EU/AUS)
		1 - Instruction Manual
Warranty Information		
	Warranty	2 År

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.