

## DVI to DisplayPort Adapter Converter with Audio - 1920x1200

**Product ID:** DVI2DPA



The DVI2DPA DVI to DisplayPort Adapter/Converter (with 2-Channel Audio) converts a DVI-D (Digital) single link, Mini-DVI or HDMI source signal and accompanying audio, for use with a DisplayPort monitor.

Supporting resolutions of up to 1920x1200, this USB-powered device offers easy plug-and-play installation with both PC and Mac platforms, ensuring seamless operation with your DisplayPort display to save the time and hassle of hardware upgrades.

A complete, out-of-the-package solution, this DVI DisplayPort adapter includes all cables necessary for connecting a DVI-D video source and accompanying audio (3.5mm stereo audio) to any DisplayPort monitor, and can also be used with Mini DVI or Mini HDMI sources using additional cables (sold separately - see Accessories).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Connect a PC DVI or HDMI output to a DisplayPort monitor
- Convert DVI video and audio to one DisplayPort input on monitors that support audio output
- Adapt a DVI-D output signal and connect supporting audio for use with Apple Cinema Displays

### Features

- Supports resolutions up to 1920x1200

- USB power, 3.5mm audio and DisplayPort cables included
- Supports stereo audio pass-through to DisplayPort output (DisplayPort audio support required on monitor)
- Stores and passes EDID information
- USB-powered operation
- No software or drivers required

---

#### Hardware

Warranty	2 Years
AV Input	DVI-D 3.5 mm Stereo Audio
AV Output	DisplayPort
Audio	Yes
Industry Standards	DisplayPort 1.1a DVI 1.0

---

#### Performance

Maximum Digital Resolutions	1920x1200
Wide Screen Supported	Yes

---

#### Connector(s)

Connector A	DVI-D (25 pin) 3.5 mm Mini-Jack (3 Position) USB Mini-B (5 pin)
Connector B	DisplayPort (20 pin)

---

#### Special Notes / Requirements

Note	Can be used with HDMI, mini HDMI or mini DVI input using an adapter - See Accessories
------	---

---

#### Indicators

LED Indicators	Power indicator
----------------	-----------------

---



## Power

Power Source	USB-Powered
Input Voltage	5 DC

---

## Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	10~85% RH

---

## Physical Characteristics

Color	Silver
Material	Aluminum and Plastic
Cable Length	24.0 in [61 cm]
Product Length	3.0 in [76.2 mm]
Product Width	2.5 in [63.5 mm]
Product Height	0.3 in [6.6 mm]
Weight of Product	7.1 oz [200 g]

---

## Packaging Information

Package Length	7.9 in [20 cm]
Package Width	7.9 in [20 cm]
Package Height	0.0 in [1 mm]
Shipping (Package) Weight	7.4 oz [210 g]

---

## What's in the Box

Included in Package	DVI to DisplayPort Converter
	3.5mm Stereo Audio cable
	USB mini B male to USB A male Cable
	DisplayPort cable



User Manual

---

***\*Product appearance and specifications are subject to change without notice.***

