

DVI to HDMI Video Adapter with USB Power and Audio - 1080p

Product ID: DVI2HD



This DVI to HDMI adapter lets you connect your DVI laptop or desktop computer to an HDMI display or projector. The adapter works with any DVI output, but when you connect it to your Windows computer, the adapter also supports native USB audio, allowing you to add your computer's audio to the HDMI output signal.

The DVI to HDMI adapter is easy to use. The adapter features plug-and-play installation, so you won't need to load or download any special software, ensuring a fast and easy installation. The adapter also features a small footprint, ensuring it discreetly blends into your desktop setup, unlike bulky DVI adapter boxes that take up a lot of desk space.

If you want to transmit video only, you can just use the DVI connection. If you want to transmit audio as well as video, you can also plug in the USB connector. With no external power adapter needed, you have everything that you need in one compact solution.

This adapter ensures that you're harnessing HD video quality from your DVI output, with support for resolutions up to 1080p.

The DVI2HD is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Make your legacy DVI device compatible with a new HDMI television or projector
- Connect a DVI computer to an HDMI display at your desktop or workstation

- Convert DVI to HDMI and add audio to the HDMI signal

Features

- Adds 2-channel stereo audio to your HDMI output with USB audio
- Hassle-free setup with plug-and-play installation
- Crystal-clear picture quality with support for HD resolutions up to 1080p
- Compact and USB powered for maximum portability

Hardware

Warranty	3 Years
AV Input	DVI-D
AV Output	HDMI
Audio	Yes
Chipset ID	LT8522EX - CM108AH

Performance

Maximum Digital Resolutions	1920 x 1080p at 60Hz
Supported Resolutions	1920x1080 (1080p)
	1680x1050 (WSXGA+)
	1600x1200
	1600x900
	1440x900
	1400x1050 (SXGA+)
	1366x768
	1360x768
	1280x1024
	1280x960
	1280x800
	1280x768 (WXGA)
	1280x720p (720p)

	1280x600
	1152x864
	1024x768
	800x600 (SVGA)
	640x480 (480p)
Wide Screen Supported	Yes
Audio Specifications	2-channel stereo audio
MTBF	1,102,819 hours

Connector(s)

Connector A	1 - DVI-D (25 pin)
Connector B	1 - HDMI (19 pin)

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 55C (14F to 131F)
Humidity	40%-50%RH

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	7.0 in [177.8 mm]
Product Length	9.8 in [25.0 cm]
Product Width	1.4 in [3.5 cm]
Product Height	0.5 in [1.3 cm]
Weight of Product	2.4 oz [69.0 g]

Packaging Information

Package Quantity	1
Package Length	6.6 in [16.8 cm]

Package Width	5.8 in [14.8 cm]
Package Height	1.3 in [3.2 cm]
Shipping (Package) Weight	4.4 oz [126.0 g]

What's in the Box

Included in Package	1 - DVI to HDMI adapter
	1 - quick install guide

****Product appearance and specifications are subject to change without notice.***