

DVI to Mini DisplayPort Adapter with Audio

Produkt ID: DVI2MDPA



The DVI2MDPA DVI to Mini DisplayPort® Adapter (with 2-Channel Audio) converts a DVI-D (Digital), Mini-DVI or HDMI source signal and accompanying audio, for use with a Mini DisplayPort or DisplayPort monitor at resolutions up to 1920x1200.

The adapter offers easy plug-and-play installation with both PC and Mac® platforms, ensuring seamless operation with your display to save the time and hassle of hardware upgrades.

A complete, out-of-the-box solution, this DVI-Mini DisplayPort adapter includes all cables necessary for connecting a DVI-D video source and 3.5mm stereo audio to any Mini DisplayPort monitor, including Apple Cinema HD® displays, and can also be used with Mini DVI or Mini HDMI sources using additional cables (sold separately - see Accessories).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet



Användning

- Use a PC with a DVI or HDMI output with a Mini-DisplayPort monitor
- Convert DVI video and audio to one Mini DisplayPort input on monitors that support audio output

- Adapt a DVI-D output signal and connect supporting audio for use with Apple Cinema Displays

Funktioner

- Supports resolutions up to 1920x1200
- USB power, 3.5mm audio and Mini-DisplayPort cables included
- Supports stereo audio pass-through to Mini-DisplayPort output (DisplayPort audio support required on monitor)
- Stores and passes EDID information
- USB-powered operation
- No software or drivers required

Hårdvara

Garantipolicy	2 Years
Active or Passive Adapter	Aktiv
AV-ingång	DVI-D
	3,5 mm stereoaudio
AV-utgång	Mini-DisplayPort
Audio	Ja
Industristandarder	Mini-DisplayPort 1.1a
	DVI 1.0

Prestanda

Maximal digital upplösning	1920x1200
Stöd för widescreen	Ja

Kontakt(er)

Connector A	1 - USB Mini-B (5-stifts)
	1 - DVI-D (25-stifts)

		1 - 3.5 mm minijack (3-polig)
	Connector B	1 - Mini-DisplayPort (20-stifts)
Särskilda anmärkningar/krav	Obs.	Can be used for HDMI input, or standard DisplayPort output using adapters - See Accessories
Indikatorer	LED-indikatorer	1 - Power indicator
Ström	Strömkälla	Strömförsörjd via USB
	Inspänning	5 DC
Miljö	Drifttemperatur	0°C to 70°C (32°F to 158°F)
	Förvaringstemperatur	-10°C to 80°C (14°F to 176°F)
	Luftfuktighet	10~85% RH
Utseende	Färg	Svart
	Kabinetttyp	Aluminium och plast
	Kabellängd	24.0 in [610 mm]
	Produktlängd	3.3 in [83 mm]
	Produktbredd	2.4 in [6.1 cm]
	Produkthöjd	0.6 in [1.4 cm]
	Produktvikt	4.1 oz [116 g]
Förpackning	Förpackningsantal	1
	Paketets längd	8.7 in [22 cm]
	Paketets bredd	7.9 in [20 cm]

Paketets höjd 1.2 in [30 mm]

Fraktvikt (förpackning) 0.5 lb [0.2 kg]

Vad det är i lådan

Ingår i paketet	1 - DVI to Mini-DisplayPort Converter
	1 - Mini DisplayPort cable
	1 - 3.5mm Stereo Audio cable
	1 - USB mini B male to 2xA male (Split) Cable
	1 - User Manual

Warranty
Information

Warranty	2 År
----------	------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.