

Cable d'extension DVI-D Dual Link de 4,6 m - Cable DVI male vers femelle avec resolution maximale de 2560 x 1600

N° de produit: DVIDDMF15



The DVIDDMF15 15ft DVI-D Dual Link Extension Cable allows you to extend the connection between your desktop workstation and DVI monitor, or your laptop and projector by up to 15-feet.

The dual link cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

This durable DVI male to female cable is designed to provide a high quality digital video experience, and is backed by StarTech.com's lifetime warranty.

Certifications, rapports et compatibilité



Applications

- Extend the connection distance between your desktop or laptop computer and a DVI-D Dual Link display or projector by up to 15ft

Spécifications techniques

- Supports a maximum resolution of 2560x1600

- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Matériel

Politique de garantie	Lifetime
Placage du connecteur	Nickel
Type de gaine de câble	PVC - Polyvinyl Chloride
Nombre de tores magnétiques	1

Connecteur(s)

Connecteur A	1 - DVI-D (25 broches)
Connecteur B	1 - DVI-D (25 broches)

Caractéristiques physiques

Couleur	Noir
Longueur de câble	15.0 ft [4.6 m]
Longueur du produit	15.0 ft [4.6 m]
Largeur du produit	0.0 in [0.0 mm]
Hauteur du produit	0.0 in [0.0 mm]
Poids du produit	1.1 lb [0.5 kg]

Informations d'emballage

Quantité par paquet	1
Longueur du Paquet	1.4 in [3.5 cm]
Largeur du Paquet	9.1 in [23.0 cm]

Hauteur du Paquet 12.6 in [32.0 cm]

Poids brut 1.1 lb [0.5 kg]

Contenu du paquet

Inclus dans le paquet 1 - 15 ft Dual Link Monitor DVI-D Extension Cable - M/F

Informations de
garantie

Warranty À Vie

* L'apparence et les spécifications du produit peuvent être modifiées sans préavis