

15 ft DVI-D Dual Link Monitor Extension Cable - M/F

Productcode: DVIDDMF15



The DVIDDMF15 15ft DVI-D Dual Link Extension Cable allows you to extend the connection between your desktop workstation and DVI monitor, or your laptop and projector by up to 15-feet.

The dual link cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

This durable DVI male to female cable is designed to provide a high quality digital video experience, and is backed by StarTech.com's lifetime warranty.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Extend the connection distance between your desktop or laptop computer and a DVI-D Dual Link display or projector by up to 15ft

Eigenschappen

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec

- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware

Garantiebeleid	Lifetime
Connectormateriaal	Nikkel
Type kabelmantel	PVC - Polyvinyl Chloride
Aantal ferrieten	1

Connector(en)

Connector A	1 - DVI-D (25-polig)
Connector B	1 - DVI-D (25-polig)

Fysieke eigenschappen

Kleur	Zwart
Kabellengte	15.0 ft [4.6 m]
Lengte product	15.0 ft [4.6 m]
Breedte product	0.0 in [0.0 mm]
Hoogte product	0.0 in [0.0 mm]
Gewicht product	1.1 lb [0.5 kg]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	1.4 in [3.5 cm]
Package Width	9.1 in [23.0 cm]
Package Height	12.6 in [32.0 cm]

	Verzendgewicht (verpakt)	1.1 lb [0.5 kg]
Wat wordt er meegeleverd	Meegeleverd	1 - 15 ft Dual Link Monitor DVI-D Extension Cable - M/F
Garantiebepalinge n	Warranty	Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.