

## 15 ft DVI-D Dual Link Monitor Extension Cable - M/F

**Product ID:** DVIDDMF15



The DVIDDMF15 15ft DVI-D Dual Link Extension Cable allows you to extend the connection between your desktop workstation and DVI monitor, or your laptop and projector by up to 15-feet.

The dual link cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

This durable DVI male to female cable is designed to provide a high quality digital video experience, and is backed by StarTech.com's lifetime warranty.

## Certifications, Reports and Compatibility

### Applications

- Extend the connection distance between your desktop or laptop computer and a DVI-D Dual Link display or projector by up to 15ft

### Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices

- Compliant with DVI DDWG Standards

---

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Number of Ferrites	1

---

**Connector(s)**

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

---

**Physical Characteristics**

Color	Black
Cable Length	15.0 ft [4.6 m]
Product Length	15.0 ft [4.6 m]
Weight of Product	18.1 oz [513 g]

---

**Packaging Information**

Package Length	1.4 in [35 mm]
Package Width	9.1 in [23 cm]
Package Height	12.6 in [32 cm]
Shipping (Package) Weight	18.1 oz [513 g]

---

**What's in the Box**

Included in Package	15 ft Dual Link Monitor DVI-D Extension Cable - M/F
---------------------	---

---

*\*Product appearance and specifications are subject to change without notice.*

