

15 ft DVI-D Dual Link Monitor Extension Cable - M/F

Product ID: DVIDDMF15



The DVIDDMF15 15ft DVI-D Dual Link Extension Cable allows you to extend the connection between your desktop workstation and DVI monitor, or your laptop and projector by up to 15-feet.

The dual link cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

This durable DVI male to female cable is designed to provide a high quality digital video experience, and is backed by StarTech.com's lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Extend the connection distance between your desktop or laptop computer and a DVI-D Dual Link display or projector by up to 15ft

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference

- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Number of Ferrites	1

Connector(s)

Connector A	1 - DVI-D (25 pin)
Connector B	1 - DVI-D (25 pin)

Physical Characteristics

Color	Black
Cable Length	15.0 ft [4.6 m]
Product Length	15.0 ft [4.6 m]
Weight of Product	18.1 oz [513 g]

Packaging Information

Package Quantity	1
Package Length	1.4 in [35 mm]
Package Width	9.1 in [23 cm]
Package Height	12.6 in [32 cm]
Shipping (Package) Weight	18.1 oz [513 g]

What's in the Box

Included in Package	1 - 15 ft Dual Link Monitor DVI-D Extension Cable - M/F
---------------------	---

**Product appearance and specifications are subject to change without notice.*

