

2m DVI-D Dual Link Monitor Extension Cable - M/F

Produkt ID: DVIDDMF2M



The DVIDDMF2M 2m DVI-D Dual Link Extension Cable allows you to extend the connection between your desktop workstation and DVI monitor, or your laptop and projector by up to 2-meters.

The dual link cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

This durable DVI male to female cable is designed to provide a high quality digital video experience, and is backed by StarTech.com's lifetime warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Extend the connection distance between your desktop or laptop computer and a DVI-D Dual Link display or projector by up to 2 meters

Funktioner

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec

- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride

Kontakt(er)

Connector A	1 - DVI-D (25-stifts)
Connector B	1 - DVI-D (25-stifts)

Utseende

Färg	Svart
Tråddimension	28 AWG
Kabellängd	6.6 ft [2 m]
Produktlängd	6.6 ft [2.0 m]
Produktbredd	1.6 in [4.0 cm]
Produkthöjd	0.6 in [1.6 cm]
Produktvikt	8.9 oz [253.0 g]

Förpackning

Förpackningsantal	1
Paketets längd	5.7 in [14.6 cm]
Paketets bredd	3.9 in [9.9 cm]
Paketets höjd	1.1 in [2.7 cm]
Fraktvikt (förpackning)	9.3 oz [263.0 g]

Vad det är i lådan

Ingår i paketet

1 - 2m DVI-D Dual Link Monitor Extension Cable - M/F

Warranty
Information

Warranty

Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.