

## 2m DVI-D Dual Link Monitor Extension Cable - M/F

**Product ID:** DVIDDMF2M



The DVIDDMF2M 2m DVI-D Dual Link Extension Cable allows you to extend the connection between your desktop workstation and DVI monitor, or your laptop and projector by up to 2-meters.

The dual link cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

This durable DVI male to female cable is designed to provide a high quality digital video experience, and is backed by StarTech.com's lifetime warranty.

### Certifications, Reports and Compatibility



### Applications

- Extend the connection distance between your desktop or laptop computer and a DVI-D Dual Link display or projector by up to 2 meters

### Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference

- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

---

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride

---

**Connector(s)**

Connector A	1 - DVI-D (25 pin)
Connector B	1 - DVI-D (25 pin)

---

**Physical Characteristics**

Color	Black
Wire Gauge	28 AWG
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]
Product Width	1.6 in [4.0 cm]
Product Height	0.6 in [1.6 cm]
Weight of Product	8.9 oz [253.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	5.7 in [14.6 cm]
Package Width	3.9 in [9.9 cm]
Package Height	1.1 in [2.7 cm]
Shipping (Package) Weight	9.3 oz [263.0 g]

---

**What's in the Box**

Included in Package      1 - 2m DVI-D Dual Link Monitor Extension Cable - M/F

---

***\*Product appearance and specifications are subject to change without notice.***

