

6 ft DVI-D Dual Link Monitor Extension Cable - M/F

Productcode: DVIDDMF6



The DVIDDMF6 6ft DVI-D Dual Link Extension Cable allows you to extend the connection between your desktop workstation and DVI monitor, or your laptop and projector by up to 6-feet.

The dual link cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

This durable DVI male to female cable is designed to provide a high quality digital video experience, and is backed by StarTech.com's lifetime warranty.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Extend the connection distance between your desktop or laptop computer and a DVI-D Dual Link display or projector by up to 6ft

Eigenschappen

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec

- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware

Garantiebeleid	Lifetime
Connectormateriaal	Nikkel

Prestaties

Algemene specificaties	Insertion Rating: 3000
------------------------	------------------------

Connector(en)

Connector A	1 - DVI-D (25-polig)
Connector B	1 - DVI-D (25-polig)

Gebruiksomgeving

Bedrijfstemperatuur	0 to 50 °C
Opslagtemperatuur	-20 to 70 °C
Vochtigheid	0 to 95%

Fysieke eigenschappen

Kleur	Zwart
Draaddikte	28 AWG
Kabellengte	6.0 ft [1.8 m]
Lengte product	6.0 ft [1.8 m]
Gewicht product	8.9 oz [252 g]

Verpakkingsinformatie

Verpakkingsaantal	1
-------------------	---

Lengte Verpakking	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	1.2 in [30 mm]
Verzendgewicht (verpakt)	9.2 oz [261 g]

Wat wordt er meegeleverd

Meegeleverd	6 ft DVI-D Dual Link Digital Video Monitor Cable - M/F
-------------	--

Garantiebepalingen

Warranty	Levenslang
----------	------------

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.