

6 ft DVI-D Dual Link Monitor Extension Cable - M/F

Product ID: DVIDDMF6



The DVIDDMF6 6ft DVI-D Dual Link Extension Cable allows you to extend the connection between your desktop workstation and DVI monitor, or your laptop and projector by up to 6-feet.

The dual link cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

This durable DVI male to female cable is designed to provide a high quality digital video experience, and is backed by StarTech.com's lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Extend the connection distance between your desktop or laptop computer and a DVI-D Dual Link display or projector by up to 6ft

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices

- Compliant with DVI DDWG Standards

Hardware

Warranty	Lifetime
Connector Plating	Nickel

Performance

General Specifications	Insertion Rating: 3000
------------------------	------------------------

Connector(s)

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

Environmental

Operating Temperature	0 to 50 C
Storage Temperature	-20 to 70 C
Humidity	0 to 95%

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Weight of Product	8.9 oz [252 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	1.2 in [30 mm]
Shipping (Package) Weight	9.2 oz [261 g]

What's in the Box



Included in Package

6 ft DVI-D Dual Link Digital Video Monitor Cable - M/F

****Product appearance and specifications are subject to change without notice.***

