

10 ft DVI-D Dual Link Cable - M/M

**Product ID:** DVIDDMM10



The DVIDDMM10 10ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 10 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

## Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

## Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Compliant with DVI DDWG Standards
- Aluminum-Mylar Foil with Braided Shielding

- Supports hot-plugging of DVI display devices

---

#### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Shield Material	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard

---

#### Connector(s)

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

---

#### Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Product Width	1.5 in [36.9 mm]
Product Height	0.6 in [16 mm]
Weight of Product	12.9 oz [366.0 g]

---

#### Packaging Information

Package Length	15.4 in [39.0 cm]
Package Width	5.3 in [13.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	13.2 oz [374.0 g]

---

#### What's in the Box

Included in Package	10 ft DVI-D Dual Link Cable - M/M
---------------------	-----------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

