

10 ft DVI-D Dual Link Cable - M/M

Product ID: DVIDDMM10



The DVIDDMM10 10ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 10 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference

- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Shield Material	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard

Connector(s)

Connector A	1 - DVI-D (25 pin)
Connector B	1 - DVI-D (25 pin)

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20 to 70C (-4F to 158F)
Humidity	0 to 95%

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Product Width	1.5 in [3.7 cm]
Product Height	0.6 in [1.6 cm]
Weight of Product	12.9 oz [366.0 g]

Packaging Information

Package Quantity	1
Package Length	15.4 in [39.0 cm]

Package Width	5.3 in [13.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	13.2 oz [374.0 g]

What's in the Box

Included in Package	1 - 10 ft DVI-D Dual Link Cable - M/M
---------------------	---------------------------------------

****Product appearance and specifications are subject to change without notice.***