

15 ft DVI-D Dual Link Cable - M/M

Produkt ID: DVIDDMM15



The DVIDDMM15 15ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 15 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Funktioner

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec

- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelskärmning	Aluminiummylarfolie med flätning
Industristandarder	DVI DDWG Standard

Kontakt(er)

Connector A	1 - DVI-D (25-stifts)
Connector B	1 - DVI-D (25-stifts)

Miljö

Drifttemperatur	0°C to 50°C (32°F to 122°F)
Förvaringstemperatur	-20 to 70°C (-4°F to 158°F)
Luftfuktighet	0 ~ 95%

Utseende

Färg	Svart
Tråddimension	28 AWG
Kabellängd	15.0 ft [4.6 m]
Produktlängd	15.0 ft [4.6 m]
Produktbredd	1.5 in [3.8 cm]
Produkthöjd	0.4 in [1.0 cm]
Produktvikt	1.1 lb [0.5 kg]

Förpackning

Förpackningsantal	1
Paketets längd	7.0 in [17.7 cm]
Paketets bredd	7.6 in [19.4 cm]
Paketets höjd	2.2 in [5.7 cm]
Fraktvikt (förpackning)	1.1 lb [0.5 kg]

Vad det är i lådan

Ingår i paketet	1 - 15 ft DVI-D Dual Link Cable - M/M
-----------------	---------------------------------------

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.