

1 ft DVI-D Dual Link Cable - M/M

**Product ID:** DVIDDMM1



The DVIDDMM1 1ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 1 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility



## Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

## Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference

- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

---

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Industry Standards	DVI DDWG Standard

---

**Connector(s)**

Connector A	1 - DVI-D (25 pin)
Connector B	1 - DVI-D (25 pin)

---

**Physical Characteristics**

Color	Black
Wire Gauge	28 AWG
Cable Length	1.0 ft [0.3 m]
Product Length	1.0 ft [0.3 m]
Product Width	1.6 in [4.0 cm]
Product Height	0.6 in [1.6 cm]
Weight of Product	3.2 oz [91.5 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]

Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	3.6 oz [102.0 g]

---

**What's in the Box**

Included in Package	1 - 1 ft DVI-D Dual Link Cable - M/M
---------------------	--------------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***