

1m DVI-D Dual Link Cable – M/M

**Product ID:** DVIDDMM1M



The DVIDDMM1M 1m DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 1m DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

## Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

## Features

- Ferrite core eliminates EMI interference
- Supports a maximum resolution of 2560x1600
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards
- Aluminum-Mylar Foil with Braided Shielding

- High-speed digital transmission rate of up to 9.9 Gbits/sec

---

#### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

#### Connector(s)

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

---

#### Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	39.4 in [100 cm]
Product Length	39.4 in [100.0 cm]
Product Width	1.6 in [39.6 mm]
Product Height	0.6 in [16 mm]
Weight of Product	7.3 oz [207.0 g]

---


#### Packaging Information

Package Quantity	1
Package Length	7.9 in [20.0 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	7.7 oz [218.0 g]

---

#### What's in the Box

Included in Package	1m DVI-D Dual Link Monitor Cable - M/M
---------------------	--



---

***\*Product appearance and specifications are subject to change without notice.***

