

20 ft DVI-D Dual Link Cable - M/M

Product ID: DVIDDMM20



The DVIDDMM20 20ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 20 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 20 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Compliant with DVI DDWG Standards
- Aluminum-Mylar Foil with Braided Shielding

- Supports hot-plugging of DVI display devices

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Shield Material	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard

Connector(s)

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	20.0 ft [6.1 m]
Product Length	20.0 ft [6.1 m]
Weight of Product	21.5 oz [609 g]

Packaging Information

Package Length	13.0 in [33 cm]
Package Width	10.0 in [25.5 cm]
Package Height	1.6 in [40 mm]
Shipping (Package) Weight	22.1 oz [627 g]

What's in the Box

Included in Package	20 ft DVI-D Dual Link Cable - M/M
---------------------	-----------------------------------

**Product appearance and specifications are subject to change without notice.*