

25 ft DVI-D Dual Link Cable - M/M

Product ID: DVIDDMM25



The DVIDDMM2525ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 25 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 25 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
 - High-speed digital transmission rate of up to 9.9 Gbits/sec
 - Ferrite core eliminates EMI interference
 - Compliant with DVI DDWG Standards
 - Aluminum-Mylar Foil with Braided Shielding
 - Supports hot-plugging of DVI display devices
-

Hardware	Warranty	Lifetime
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
	Fire Rating	CMG Rated (General Purpose)
	Number of Ferrites	2
	Industry Standards	DVI DDWG Standard
Connector(s)	Connector A	DVI-D (25 pin)
	Connector B	DVI-D (25 pin)
Physical Characteristics	Color	Black
	Wire Gauge	28 AWG
	Cable Length	25.0 ft [7.6 m]
	Product Length	25.0 ft [7.6 m]
	Weight of Product	26.9 oz [763 g]
Packaging Information	Package Length	9.4 in [2.4 cm]
	Package Width	2.2 in [56 mm]
	Package Height	11.8 in [3 cm]
	Shipping (Package) Weight	26.9 oz [763 g]
What's in the Box	Included in Package	25 ft DVI-D Dual Link Cable - M/M

**Product appearance and specifications are subject to change without notice.*

