

2m DVI-D Dual Link Cable – M/M

Product ID: DVIDDMM2M



The DVIDDMM2M 2mDVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 2m DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
 - High-speed digital transmission rate of up to 9.9 Gbits/sec
 - Ferrite core eliminates EMI interference
 - Compliant with DVI DDWG Standards
 - Aluminum-Mylar Foil with Braided Shielding
 - Supports hot-plugging of DVI display devices
-

Hardware	Warranty	Lifetime
	Number of Conductors	24
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
	Fire Rating	CMG Rated (General Purpose)
	Number of Ferrites	2
	Industry Standards	DVI DDWG Standard
Connector(s)	Connector A	DVI-D (25 pin)
	Connector B	DVI-D (25 pin)
Physical Characteristics	Color	Black
	Connector Style	Straight
	Wire Gauge	28 AWG
	Cable Length	6.6 ft [2 m]
	Cable OD	0.3 in [8.6 mm]
	Product Length	6.6 ft [2.0 m]
	Product Width	1.6 in [39.6 mm]
	Product Height	0.6 in [16 mm]
	Weight of Product	10.6 oz [300.000 g]
Packaging Information	Package Quantity	1
	Package Length	7.9 in [2.0 cm]
	Package Width	8.7 in [2.2 cm]
	Package Height	0.0 in [0.100 mm]
	Shipping (Package) Weight	10.9 oz [308.000 g]
What's in the Box	Included in Package	2m DVI-D Dual Link Digital Video Monitor Cable - M/M

**Product appearance and specifications are subject to change without notice.*

