

3 ft DVI-D Dual Link Cable - M/M

Product ID: DVIDDMM3



The DVIDDMM3 3ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 3 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices

- Compliant with DVI DDWG Standards

Prominence

Warranty	Lifetime
Description	CDW 75 - 1st StarTech.com 3 ft DVI-D Dual Link Cable - M/M - 3ft - 3ft Dual Link DVI Line

Hardware

Connector Plating	Nickel
Cable Shield Material	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard

Connector(s)

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	36.0 in [91.4 cm]
Product Length	36.0 in [91.5 cm]
Product Width	1.6 in [39.6 mm]
Product Height	0.6 in [16 mm]
Weight of Product	7.2 oz [203.0 g]

Packaging Information

Package Length	7.9 in [20.0 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	7.5 oz [213.0 g]



**What's in the
Box**

Included in Package 3 ft DVI-D Dual Link Cable - M/M

****Product appearance and specifications are subject to change without notice.***

