

40 ft DVI-D Dual Link Cable - M/M

**Product ID:** DVIDDMM40



The DVIDDMM40 40ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 40 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 40 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

### Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

### Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Compliant with DVI DDWG Standards
- Aluminum-Mylar Foil with Braided Shielding

- Supports hot-plugging of DVI display devices

---

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel
Industry Standards	DVI DDWG Standard

---

**Connector(s)**

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

---

**Physical Characteristics**

Color	Black
Wire Gauge	28 AWG
Cable Length	40.0 ft [12.2 m]
Product Length	40.0 ft [12.2 m]
Weight of Product	2.5 lb [1.1 kg]

---

**Packaging Information**

Package Length	8.7 in [22 cm]
Package Width	8.7 in [22 cm]
Package Height	2.4 in [60 mm]
Shipping (Package) Weight	2.5 lb [1.1 kg]

---

**What's in the Box**

Included in Package	40 ft DVI-D Dual Link Cable - M/M
---------------------	-----------------------------------

---

*\*Product appearance and specifications are subject to change without notice.*

