

50 ft DVI-D Dual Link Cable - M/M

Produkt-ID: DVIDDMM50



The DVIDDMM50 50ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 50 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 50 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Kompatibel mit Flachbildschirmen, digitalen CRT-Displays, Projektoren und HDTVs

Merkmale

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec

- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware

Garantiebestimmungen	Lifetime
Industrienormen	DVI DDWG Standard

Steckverbinder

Steckverbinder A	1 - DVI-D (25-polig)
Steckverbinder B	1 - DVI-D (25-polig)

Umgebungsbedingungen

Betriebstemperatur	0°C to 50°C (32°F to 122°F)
Lagertemperatur	-20 to 70°C (-4°F to 158°F)
Feuchtigkeit	0 bis 95%

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	28 AWG
Kabellänge	50.0 ft [15.2 m]
Produktlänge	50.0 ft [15.2 m]
Produktgewicht	3.0 lb [1.4 kg]

Verpackungsinformationen

Paketmenge	1
Paketlänge	9.8 in [24.9 cm]
Paketbreite	10.0 in [25.4 cm]

Pakethöhe 2.9 in [7.4 cm]

Versandgewicht
(Verpackung) 3.0 lb [1.4 kg]

Verpackungsinhalt

Im Paket enthalten 1 - 50 ft DVI-D Dual Link Cable - M/M

Garantieinformationen

Warranty Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.