

50 ft DVI-D Dual Link Cable - M/M

Productcode: DVIDDMM50



The DVIDDMM50 50ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 50 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 50 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Compatibel met LCD-schermen, CRT-schermen, projectoren en HDTV

Eigenschappen

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec

- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware

Garantiebeleid	Lifetime
Industriestandaarden	DVI DDWG Standard

Connector(en)

Connector A	1 - DVI-D (25-polig)
Connector B	1 - DVI-D (25-polig)

Gebruiksomgeving

Bedrijfstemperatuur	0°C to 50°C (32°F to 122°F)
Opslagtemperatuur	-20 to 70°C (-4°F to 158°F)
Vochtigheid	0 tot 95%

Fysieke eigenschappen

Kleur	Zwart
Draaddikte	28 AWG
Kabellengte	50.0 ft [15.2 m]
Lengte product	50.0 ft [15.2 m]
Gewicht product	3.0 lb [1.4 kg]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	9.8 in [24.9 cm]
Package Width	10.0 in [25.4 cm]

Package Height 2.9 in [7.4 cm]

Verzendgewicht
(verpakt) 3.0 lb [1.4 kg]

Wat wordt er
meegeleverd

Meegleverd 1 - 50 ft DVI-D Dual Link Cable - M/M

Garantiebepalinge
n

Warranty Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.