

50 ft DVI-D Dual Link Cable - M/M

**Product ID:** DVIDDMM50



The DVIDDMM50 50ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 50 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 50 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

## Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

## Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices

- Compliant with DVI DDWG Standards

---

**Hardware**

Warranty	Lifetime
Industry Standards	DVI DDWG Standard

---

**Connector(s)**

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

---

**Environmental**

Operating Temperature	0C to 40C (32F to 104F)
-----------------------	-------------------------

---

**Physical Characteristics**

Color	Black
Wire Gauge	28 AWG
Cable Length	50.0 ft [15.2 m]
Product Length	50.0 ft [15.2 m]
Weight of Product	3.0 lb [1.4 kg]

---

**Packaging Information**

Package Length	12.6 in [32 cm]
Package Width	9.8 in [25 cm]
Package Height	2.8 in [70 mm]
Shipping (Package) Weight	3.0 lb [1.4 kg]

---

**What's in the Box**

Included in Package	50 ft DVI-D Dual Link Cable - M/M
---------------------	-----------------------------------

---

*\*Product appearance and specifications are subject to change without notice.*

