

## 6 ft 90° Upward Angled Dual Link DVI-D Monitor Cable - M/M

Product ID: DVIDDMMTA6



The DVIDDMMTA6ft Dual Link DVI-D cable features a standard DVI-D dual link connector as well as a DVI-D dual link connector that is situated on an upward angle relative to the shaft of the cable, requiring only 40mm of space at the connection point.

The perfect solution for making digital video connections in tight spaces, the design of the upwardangle cable connector helps prevent damage to the cable and ensures long-lasting performance by eliminating the need to bend or strain the cable to account for a lack of space.

The 6ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Compatibel met LCD-schermen, CRT-schermen, projectoren en HDTV

### Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Voldoet aan de DVI DDWG-specificaties

- Aluminum-Mylar folie met gevlochten afscherming
- Ondersteunt hot-plugging van DVI-beeldschermen
- 90 Upward Angled connector with a 40mm depth
- Ferrietkern elimineert EMI-interferentie

<b>Hardware</b>	Warranty	Lifetime
	Type kabelmantel	PVC - Polyvinyl Chloride
	Industriestandaarden	DVI DDWG Standard
<b>Connector(en)</b>	Connector A	DVI-D (25 pin)
	Connector B	DVI-D (25 pin)
<b>Fysieke eigenschappen</b>	Kleur	Black
	Draaddikte	28 AWG
	Kabellengte	6.0 ft [1.8 m]
	Buitendiameter kabel	0.3 in [8.6 mm]
	Lengte product	6.0 ft [1.8 m]
	Gewicht product	7.7 oz [218 g]
<b>Verpakkingsinformatie</b>	Package Length	7.9 in [2 cm]
	Package Width	0.0 in [1 mm]
	Package Height	8.3 in [2.1 cm]
	Verzendgewicht (verpakt)	8.5 oz [240 g]
<b>Wat wordt er meegeleverd</b>	Meegeleverd	6ft Up Angled DVI-D Dual Link Digital Monitor Cable

*\*Product appearance and specifications are subject to change without notice.*

