

10 ft DVI-D Single Link Monitor Extension Cable - M/F

Produkt ID: DVIDSMF10



The DVIDSMF10 DVI-D Single-Link Monitor Extension Cable allows you to extend the connection between your desktop workstation and DVI monitor, or your laptop and projector by up to 10-feet.

The single-link cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

This durable DVI male to female cable is designed to provide a high quality digital video experience, and is backed by StarTech.com's lifetime warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Extend the connection distance between your desktop or laptop computer and a DVI-D Single Link display or projector by up to 10ft

Funktioner

- Supports a maximum resolution of 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec

- Aluminum-Mylar Foil with Braided Shielding
- Supports hot plugging of DVI display devices
- Compliant with DVI DDWG Standards
- Molded connectors with strain relief

Hårdvara

Garantipolicy	Lifetime
Industristandarder	DVI DDWG Standard

Kontakt(er)

Connector A	1 - DVI-D (19-stifts)
Connector B	1 - DVI-D (25-stifts)

Utseende

Färg	Svart
Tråddimension	28 AWG
Kabellängd	10.0 ft [3.0 m]
Produktlängd	10.0 ft [3.0 m]
Produktvikt	9.4 oz [266 g]

Förpackning

Förpackningsantal	1
Paketets längd	6.9 in [17.6 cm]
Paketets bredd	7.7 in [19.5 cm]
Paketets höjd	1.7 in [4.2 cm]
Fraktvikt (förpackning)	9.8 oz [278.0 g]

Vad det är i lådan

Ingår i paketet	10 ft DVI-D Single Link Monitor Extension Cable - M/F
-----------------	---

Warranty

Information

Warranty

Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.