

20 ft DVI-D Single Link Cable - M/M

ID prodotto: DVIDSMM20



The DVIDSMM20 DVI-D Single Link cable features 2 male DVI (19-pin) connectors and offers 20 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 20ft DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certificazioni, report e compatibilità



Applicazioni

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

Caratteristiche

- Supports resolutions up to 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec

- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware

Norme di garanzia	Lifetime
Placcatura connettori	Nichel
Tipo guaina cavo	PVC - Polyvinyl Chloride
Tipo schermatura cavo	Foglio di alluminio mylar con treccia
Standard del settore	DVI DDWG Standard

Connettore/i

Connettore A	1 - DVI-D (19 pin)
Connettore B	1 - DVI-D (19 pin)

Caratteristiche fisiche

Colore	Nero
Diametro filo	28 AWG
Lunghezza del cavo	20.0 ft [6.1 m]
Lunghezza prodotto	20.0 ft [6.1 m]
Larghezza prodotto	0.0 in [0.0 mm]
Altezza prodotto	0.0 in [0.0 mm]
Peso prodotto	15.9 oz [450.0 g]

Informazioni confezione

Quantità confezione	1
Lunghezza Confezione	12.6 in [32.0 cm]
Package Width	9.9 in [25.2 cm]

Package Height 0.2 in [6.0 mm]

Peso spedizione
(confezione) 1.0 lb [0.5 kg]

Contenuto della
confezione

Incluso nella
confezione 1 - 20ft DVI-D Single Link Cable - M/M

* L'aspetto e le specifiche dell'articolo sono soggetti a modifiche senza preavviso.