

20 ft DVI-D Single Link Cable - M/M

Product ID: DVIDSMM20

The DVIDSMM20 DVI-D Single Link cable features 2 male DVI (19-pin) connectors and offers 20 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 20ft DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

Features

- Supports resolutions up to 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards
- Aluminum-Mylar Foil with Braided Shielding

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard

Connector(s)

Connector A	DVI-D (19 pin)
Connector B	DVI-D (19 pin)



**Physical
Characteristics**

Color	Black
Wire Gauge	28 AWG
Cable Length	20.0 ft [6.1 m]
Product Length	20.0 ft [6.1 m]
Weight of Product	15.9 oz [450 g]

**Packaging
Information**

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	1.7 in [43 mm]
Shipping (Package) Weight	16.2 oz [459 g]

**What's in the
Box**

Included in Package	20ft DVI-D Single Link Cable - M/M
---------------------	------------------------------------

****Product appearance and specifications are subject to change without notice.***

