

## 30 ft DVI-D Single Link Cable - M/M

### Product ID: DVIDSMM30

The DVIDSMM30 DVI-D Single Link cable features 2 male DVI (19-pin) connectors and offers 30 feet in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 30ft DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

### Applications

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

### Features

- Supports resolutions up to 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards
- Aluminum-Mylar Foil with Braided Shielding

---

#### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard

---

#### Connector(s)

Connector A	DVI-D (19 pin)
Connector B	DVI-D (19 pin)



---

**Physical  
Characteristics**

Color	Black
Wire Gauge	28 AWG
Cable Length	30.0 ft [9.1 m]
Product Length	30.0 ft [9.1 m]
Weight of Product	23.1 oz [655 g]

---

**Packaging  
Information**

Package Length	13.0 in [33 cm]
Package Width	10.0 in [25.5 cm]
Package Height	1.8 in [45 mm]
Shipping (Package) Weight	23.7 oz [672 g]

---

**What's in the  
Box**

Included in Package	30ft DVI-D Single Link Cable - M/M
---------------------	------------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

