

6 ft DVI-D Single Link Cable with 3.5mm Audio - M/M

Product ID: DVIDSMM6A



The DVIDSMM6A 6ft Single-Link DVI-D display Cable with Audio features 2 male DVI (19-pin) connectors and includes a built-on audio cable with 2 male 3.5mm connectors, providing both sound and high quality video in a single cable.

The 6 ft DVI-D cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video with audio cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

Features

- Supports a maximum resolution of 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware

Warranty	Lifetime
Industry Standards	DVI DDWG Standard

Performance

Maximum Data Transfer Rate	4.95 Gbits/sec
----------------------------	----------------

Connector(s)

Connector A	3.5 mm Mini-Jack (3 Position) DVI-D (19 pin)
Connector B	3.5 mm Mini-Jack (3 Position) DVI-D (19 pin)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]

Packaging Information

Package Length	7.9 in [20 cm]
Package Width	1.2 in [30 mm]
Package Height	8.3 in [21 cm]
Shipping (Package) Weight	8.5 oz [240 g]

**Product appearance and specifications are subject to change without notice.*

