

10 ft DVI-I Dual Link Digital Analog Monitor Extension Cable M/F

Product ID: DVIIDMF10



The DVIIDMF10 DVI-I Dual-Link Digital Analog Monitor Extension Cable allows you to extend the connection distance between your DVI-I devices by up to 10-feet.

The dual link cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Extend the connection distance between your desktop or laptop computer and a DVI-I Dual Link display or projector by up to 10ft

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Compliant with DVI DDWG Standards
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot plugging of DVI display devices
- Supports both analog and digital displays

Hardware	Warranty	Lifetime
	Industry Standards	DVI DDWG Standard
Performance	Maximum Data Transfer Rate	9.9 Gbits/sec
Connector(s)	Connector A	DVI-I (29 pin)
	Connector B	DVI-I (29 pin)
Physical Characteristics	Color	Black
	Wire Gauge	28 AWG
	Cable Length	10.0 ft [3.0 m]
	Product Length	10.0 ft [3.0 m]
	Product Width	0.0 in [0.000 mm]
	Product Height	0.0 in [0.000 mm]
	Weight of Product	14.7 oz [416.000 g]
Packaging Information	Package Length	4.8 in [1.2 cm]
	Package Width	0.9 in [23.000 mm]
	Package Height	15.2 in [3.8 cm]
	Shipping (Package) Weight	14.7 oz [416.000 g]
What's in the Box	Included in Package	10 ft DVI-I Dual Link Digital Analog Monitor Extension Cable M/F

**Product appearance and specifications are subject to change without notice.*

