

## 10 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

**Product ID:** DVIIDMM10



The DVIIDMM10 10ft DVI-I Dual Link cable features 2 male DVI-I (29-pin) connectors and provides a reliable connection between your desktop or laptop computer and a DVI-I monitor or projector.

The 10ft DVI-I male to male cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

### **Certifications, Reports and Compatibility**

### **Applications**

- Connect your desktop or laptop computer to a DVI-I Dual Link display or projector

### **Features**

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices

- Compliant with DVI DDWG Standards
- Supports both analog and digital displays

---

#### Hardware

Warranty	Lifetime
Industry Standards	DVI DDWG Standard

---

#### Performance

Maximum Data Transfer Rate	9.9 Gbits/sec
----------------------------	---------------

---

#### Connector(s)

Connector A	DVI-I (29 pin)
Connector B	DVI-I (29 pin)

---

#### Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Weight of Product	15.8 oz [449 g]

---

#### Packaging Information

Package Length	15.6 in [39.5 cm]
Package Width	5.5 in [14 cm]
Package Height	0.9 in [22 mm]
Shipping (Package) Weight	16.2 oz [458 g]

---

#### What's in the Box

Included in Package	10 ft DVI-I Dual Link Digital Analog Monitor Cable M/M
---------------------	--

---

***\*Product appearance and specifications are subject to change without notice.***