

## 15 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

Product ID: DVIIDMM15



The DVIIDMM15 15ft DVI-I Dual Link cable features 2 male DVI-I (29-pin) connectors and provides a reliable connection between your desktop or laptop computer and a DVI-I monitor or projector.

The 15ft DVI-I male to male cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Connect your desktop or laptop computer to a DVI-I Dual Link display or projector

### Features

- Supports a maximum resolution of 2560x1600
  - High-speed digital transmission rate of up to 9.9 Gbits/sec
  - Aluminum-Mylar Foil with Braided Shielding
  - Supports both analog and digital displays
  - Supports hot-plugging of DVI display devices
  - Compliant with DVI DDWG Standards
  - Ferrite core eliminates EMI interference
-

<b>Hardware</b>	Warranty	Lifetime
	Industry Standards	DVI DDWG Standard
<b>Performance</b>	Maximum Data Transfer Rate	9.9 Gbits/sec
<b>Connector(s)</b>	Connector A	DVI-I (29 pin)
	Connector B	DVI-I (29 pin)
<b>Physical Characteristics</b>	Color	Black
	Wire Gauge	28 AWG
	Cable Length	15.0 ft [4.6 m]
	Product Length	15.0 ft [4.6 m]
	Weight of Product	20.3 oz [574 g]
<b>Packaging Information</b>	Package Length	13.0 in [3.3 cm]
	Package Width	10.0 in [2.6 cm]
	Package Height	3.0 in [76 mm]
	Shipping (Package) Weight	20.9 oz [591 g]
<b>What's in the Box</b>	Included in Package	15 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

***\*Product appearance and specifications are subject to change without notice.***

